

Vacuum Cleaner LXT®

DCL284F

18V, 180 mbar, 0.73 L

This is a cordless cleaner powered by 18V LXT Li-Ion battery.

High power and low noise: Other main features and benefits are: Switch: One-touch push button, Dust collection system: Capsule type.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	1,2 m³/min
Max. sealed suction	180 mbar
Tank Capacity for Dust	0,73 L
Sound Pressure Level (L _{pA})	54 / 60 / 62 / 65 dB (A)
Vibration Level (3 axes)	0,1 m/s²
Tool weight with battery	1,3 - 1,6 kg
Product Dimensions (L x W x H):	1066 x 113 x 153 mm
Continuous Use 18V / 3.0 Ah Battery	38 / 21 / 15 / 8 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	20 / 45 / 70 / 125 W
Product net weight	1,0 kg

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- Ergonomic soft grip handle provides increased comfort
- Quiet cleaning achieved by redesigning air flow structure

Link to product - www.makitauk.com



Related products

Optional AC

123539-7 Floor T-Nozzle 225 mm, Black		127828-2 Nozzle Assembly	
140H94-2 Soft Brush 360 Complete Set, Blue		1910D5-0 Cyclone Pre-separator	
1910Y3-1 TELESCOPIC PIPE SET		191D73-9 Cyclone Pre-Separator 400 ml	
191D75-5 Cyclone Attachment Set		191D77-1 Straight Pipe	
191E30-3 Flexible Hose Set		198990-0 Long sash nozzle set	
413809-5 Sash Nozzle		458942-6 Suction Tube With Pipe Lock	
459038-6 Nozzle Holder Black			

Other

User manual

Parts drawing