

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 female contact carrier,
straight

Contact carrier, Ethernet, 8-position, Socket, straight, M12, X-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1081252
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQBGH
Product key	ABQBGH
GTIN	4055626808130
Weight per piece (including packing)	7.07 g
Weight per piece (excluding packing)	4.011 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Data
Sensor type	Ethernet
Number of positions	8
Seal present	no
Shielded	yes
Coding	X
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$> 100 \text{ M}\Omega$
Nominal voltage U_N	50 V AC
	60 V DC
Nominal current I_N	0.5 A (Data)
Transmission characteristics (category)	CAT6 _A

Connection data

Connection method	SMD reflow
-------------------	------------

Interfaces

Signal type/category	Ethernet
----------------------	----------

Material specifications

Material Contact carrier	PA
Material Contact	CuZn
Material Contact surface	Au
Material Shield crossover	GD-Zn/Ni
Flammability rating according to UL 94	V0

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	X

Cable/line

Signal type/category	Ethernet
----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-55 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-109

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad


SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Drawings



Pin assignment M12 connector, 8-pos., view socket side

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1081252>

 cUL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

 UL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/gb/products/1081252>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk