


Flow control valve


ASC Series





Symbol



Inner structure




Flow chart




Dimensions

ASC100\ASC200



ASC300



Model\Item	A	B	C	CA	CB	CD	D	E	F	K	KA	KB	L	P	PA
ASC10006	32	18	52.5	47	26	8.6	23	M6×0.5	M12×0.75	4.3	22	18	M4×0.7	1/8"	10
ASC20008	36	18	56.5	51	30	8.6	27	M6×0.5	M12×0.75	4.3	26	23	M4×0.7	1/4"	13.5
ASC30010	50	28	74	65	40.5	10	37	M8×0.75	M16×1.0	5.3	35	32	M4×0.7	3/8"	17.5
ASC30015	50	28	74	65	40.5	10	37	M8×0.75	M16×1.0	5.3	35	32	M4×0.7	1/2"	17.5

Specification

Model		ASC100-06	ASC200-08	ASC300-10	ASC300-15
Fluid		Air (to be filtered by 40 μm filter element)			
Port size [Note1]		1/8"	1/4"	3/8"	1/2"
Pressure range		0.05~0.95MPa(7~135psi)			
Proof pressure		1.5MPa(215psi)			
Temperature		-20~70℃			
Material of body		Aluminum alloy			
Flow (L/min)	Control flow	200	450	1250	1650
	Free flow	400	800	1500	2500

[Note1] PT thread, G thread and NPT thread are available.

Product feature

1. Small and compact structure.
2. Allows air to exhaust and cut off air flow. The adjustment screw is both sensitive and precise.
3. Can be mounted in various position to facilitate installation and application.

Ordering code

ASC 300 10 □				
	①	②	③	④
①Model	②Code	③Port size	④Thread type	
ASC: Flow control valve	100: 100 series	06: 1/8"	Blank: PT G: G T: NPT	
	200: 200 series	08: 1/4"		
	300: 300 series	10: 3/8"		
		15: 1/2"		