

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERCLENS TRIGGER
Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Not classified
Health:	Eye irritation, category 2 Causes serious eye irritation.
Environment:	Not classified

Classification according to 67/548/EEC or 1999/45/EC:

Health:	Not classified
Physical:	Not classified
Environment:	Not classified
Other hazards :	Not classified

2.2. Label elements



Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

Labelling according to Regulation (EC) No 1272/2008

Hazard pictogram(s):



Signal word:	Warning
Hazard statement(s):	H319 : Causes serious eye irritation.
Precautionary statement(s):	P101 : If medical advice is needed, have product container or label at hand. P102 : Keep out of reach of children. P280 : Wear protective gloves/protective clothing/eye protection/face protection. P305/351/338 : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337/313 : If eye irritation persists: Get medical advice/attention. P501-2 : Dispose of contents/container to an authorised waste collection point.

Regulation (EC) No 648/2004 on detergents: aliphatic hydrocarbons < 5 %
anionic surfactants < 5 %
perfumes benzyl alcohol, limonene

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
(2-methoxymethylethoxy)propanol	34590-94-8	252-104-2	5-10	-	-	A
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	64742-47-8	(926-141-6)	1-5	Xn	65-66	B
Glycine, N-methyl-N-(1-oxododecyl)-, sodium salt	137-16-6	205-281-5	<3	T	23-38-41	
ammonia %	1336-21-6	215-647-6	0-1	C,N	34-50	
Explanation notes						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
(2-methoxymethylethoxy)propanol	01-2119450011-60	34590-94-8	252-104-2	5-10	-	-	A
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119456620-43	64742-47-8	(926-141-6)	1-5	Asp. Tox. 1	H304	B

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

Glycine, N-methyl-N-(1-oxododecyl)-, sodium salt		137-16-6	205-281-5	<3	Skin Irrit. 2, Eye Irrit. 2, Acute Tox. 3	H315,H319,H331	
ammonia %		1336-21-6	215-647-6	0-1	Skin Corr. 1B, Aquatic Acute 1	H314,H400	

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	If substance has got into eyes, immediately wash out with water for at least 15 minutes Remove contact lenses, if present and easy to do. Continue rinsing. Seek medical advice
Contact with skin :	Wash with water and soap. Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting Seek medical advice

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	May cause irritation. Symptoms : sore throat, cough
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain, impaired vision

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures**5.1. Extinguishing media**

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

May give off noxious and toxic fumes in a fire

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes
Wear breathing apparatus

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.
Ensure adequate ventilation
Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.
Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed, in a cool, well ventilated place.
Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product.
	Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
hands and skin :	Wear suitable protective gloves against chemicals
Recommended gloves:	Nitrile
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Liquid.
colour :	Off-white.
odour :	Characteristic odor.
pH :	9.25
Boiling point/range :	100 °C
Flash point :	75 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	15 %
lower limit :	0.6 %
Vapour pressure :	Not available.
Relative density :	1 g/cm3 (@ 20°C).
Solubility in water :	Soluble in water
Auto-ignition :	207 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

In case of fire, do not breathe fumes
May give off noxious and toxic fumes in a fire

10.4. Conditions to avoid

heat

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation :	May cause irritation.
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	May cause irritation.
Eye contact :	Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 4000 mg/kg
		LD50 derm.rabit	9510 mg/kg
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	64742-47-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	EC50 daphnia	1919 mg/l
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	64742-47-8	IC50 algae	1000 mg/l
		LC50 fish	1000 mg/l
		EC50 daphnia	1000 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Soluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number : Not classified as hazardous for transport

14.2. UN proper shipping name

Proper shipping name: Not applicable.

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

14.3. Transport hazard class(es)

Class: Not applicable.
Subsidiary risk: Not applicable.
ADR/RID - Classification code: Not applicable.

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: Not applicable.
IMDG - Ems: Not applicable.
IATA/ICAO - PAX: Not applicable.
IATA/ICAO - CAO: Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R23: Toxic by inhalation.
R34: Causes burns.
R38: Irritating to skin.
R41: Risk of serious damage to eyes.

Productname : AMBERCLENS TRIGGER
Ref.Nr.: UDS000291_3_20150518 (EN)

Creationdate : 18.05.15 Version : 1.0
Replaces: UK10215

R50: Very toxic to aquatic organisms.
R65: Harmful: may cause lung damage if swallowed.
R66: Repeated exposure may cause skin dryness or cracking.

*Explanation hazard statements: - : -

H304 : May be fatal if swallowed and enters airways.
H314 : Causes severe skin burns and eye damage.
H315 : Causes skin irritation.
H319 : Causes serious eye irritation.
H331 : Toxic if inhaled.
H400 : Very toxic to aquatic life.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.