



### Main

Range	New Unica
Accessory / separate part category	Adaptation accessory
Product or component type	Rocker
Number of modules	2 modules
Device presentation	Rocker
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

### Complementary

Product destination	Switch
Surface finish	Matt
Material	Thermoplastic ABS-UV stabilised: rocker
Depth	9 mm
Width	45 mm
Height	45 mm
Net weight	0.004 kg
Type of packing	Flow-pack
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

IK degree of protection	IK04
IP degree of protection	IP20

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins