

RS Pro Datasheet

ENGLISH

Flexible twin hose for acetylene and oxygen.

Specially designed dividing groove allows easy separation for fitting to gas cylinder or welding gun.

For use throughout industry for transporting acetylene and oxygen in mobile and stationary autogenic welding equipment.

Normally installed using hose clamps and specially designed brass fittings.

Please contact Codan for further information.

Application: Acetylene / Oxygen

Standard Length: 25 metres

Working Temperature: -40°C to 100°C

Inside: EPDM Colour: Black

Reinforcement: Polyester

Outside: EPDM Colour: Red/Blue

Standards: ISO 3821**

Inside dia. (mm)	Outside dia. (mm)	Working Pressure BAR	Burst Pressure BAR	Bend Radius (mm)	Weight (g/m)
5,0	11,4	20	60	45	260
6,0	15,2	20	60	75	415
6,0	16,4	20	60	80	480
6,3	13,5	20	60	60	340
8,0	15,2	20	60	75	410
9,5	16,7	20	60	90	450