


Geberit Mapress Stainless Steel T-piece, equal (silicone-free)



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For grey and black water with a pH value ≥ 5.5

- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	α°	L cm	L1 cm	I cm	Z cm	Z1 cm
81002	12	15	90	6.4	3.9	3.2	1.2	1.9
81003	15	18	90	6.8	4.1	3.4	1.4	2.1
81004	20	22	90	7.4	4.4	3.7	1.6	2.3
81005	25	28	90	8.4	5	4.2	1.9	2.7

Art. no.	DN	d _ø mm	arc °	L cm	L1 cm	I cm	Z cm	Z1 cm
81006	32	35	90	10	5.7	5	2.4	3.1
81007	40	42	90	11.4	6.5	5.7	2.7	3.5
81008	50	54	90	13.8	7.7	6.9	3.4	4.2
81009	65	76.1	90	23	11	11.5	6.2	5.7
81010	80	88.9	90	26	12.7	13	7	6.7
81011	100	108	90	31	15.3	15.5	8	7.8