



Connectors > Lighting Connectors > Ballast Connectors > Miniature Headers, SlimSeal



Number of Positions: 3
Lighting Product Type: **Connector**
Connector System: **Wire-to-Board**
Centerline (Pitch): **2.5 mm**
Sealable: **Yes**

[All Miniature Headers, SlimSeal \(8\)](#)

Features

Product Type Features

Lighting Product Type	Connector
Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Rows	1
Number of Positions	3

Electrical Characteristics

Operating Voltage (Max)	250 VAC
-------------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features



Contact Current Rating (Max)	5 A
------------------------------	-----

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.5 mm
--------------------	--------

Dimensions

Wire Size	18 – 22 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL 1977

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-2834074-3
3P PLUG, MINIATURE WATERPROOF CONN, WHITE



TE Part # 1-2834182-2
3P, PLUG CABLE ASSY-200MM, WHITE, TIN

Also in the Series | SlimSeal Miniature Connectors



Ballast Connectors(36)


Customers Also Bought



TE Part #2325347-2
Power Versa-Lock INTERFACE SEAL, 1X2



TE Part #1-2378159-2
Power Versa-Lock PLUG, 1X2 KEY A



TE Part #1676153-3
RN 0805 10K 0.1% 10PPM 5KRL



TE Part #2-1825059-4
ADF05STTR04=DIP S, FLUSH, SMT-GW



TE Part #DTM13-12PA
HDR, 12P, GRY, RA, SN/NI/CU, A



TE Part #T4140012041-000
M12, REAR MOUNTING, MALE, A CODE, 4P



TE Part #2325349-2
Power Versa-Lock REAR SEAL, 1X2, LargeID



TE Part #1-2378158-2
Power Versa-Lock CAP, 1X2 KEY A



Documents

Product Drawings

[3P REC, IP67 R/A SMT CONN,NATURE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2834236-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2834236-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2834236-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SlimSeal Connector Miniature Series](#)

English

[SlimSeal Connector Miniature Series](#)

Product Specifications

[Application Specification](#)

English