

Product data sheet

Specifications



Control module, TeSys Giga, 200-500V AC/DC, for LC1G115-225/4P advanced version

LX1G4QLSEA

Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1G
Poles description	4P
Range compatibility	TeSys G LX1G contactor coil
Product compatibility	LC1G115...225
[Uc] control circuit voltage	200...500 V AC/DC 50/60 Hz
Operating time	20...35 ms opening 40...55 ms closing
Mechanical durability	5 Mcycles
Maximum operating rate	600 cyc/mn 60 °C

Complementary

Coil technology	Built-in bidirectional peak limiting
Control circuit voltage limits	Operational: 0.8...1.1 Uc (at 60 °C) Drop-out: 0...0.45 Uc (at 60 °C)
Connections - terminals	Control circuit: push-in termination 1 cable(s) 0.2...2.5 mm ² solid stranded without cable end sleeve AWG 26...AWG 12 Control circuit: push-in termination 1 cable(s) 0.25...2.5 mm ² flexible with cable end sleeve AWG 24...AWG 14 Control circuit: push-in termination 2 cable(s) 0.5...1.0 mm ² rigid or stranded with cable end sleeve AWG 20...AWG 18
Inrush power in VA	255 VA at 480 V AC, 60 Hz
Inrush power in W	155.0 W DC
Hold-in power consumption in VA	13.4 VA at 480 V AC, 60 Hz
Hold-in power consumption in W	3.4 W for DC network

Environment

IP degree of protection	IP20 conforming to IEC 60529
Operating altitude	3000 m without derating 5000 m with derating factor
Electromagnetic compatibility	EMC immunity conforming to IEC 60947-4-1 Emission tests criteria A conforming to IEC 60947-4-1 Immunity to radiated radio-electrical interference - test level: 20 V/m conforming to EN/IEC 61000-4-3 Voltage dips and interruptions immunity test conforming to SEMI F47
Standards	EN/IEC 60947-4-1 UL 60947-4-1A CSA C22.2 No 60947-4-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at U _c
Height	144.5 mm
Width	140.7 mm
Depth	94.0 mm
Quantity per set	1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.0 cm
Package 1 Width	22.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	1.6 kg
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.8 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	6fbdad13-bb7c-47d4-a6d6-d82dd6f54349
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Halogen-free status	Halogen free plastic parts product
PVC free	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Installation

Installation Videos

[TeSys Giga - How to replace control module](#)