

Enamelled copper wire on mini bobbin
CUL 100/0,15



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 100/0,15**

Type	CUL 100/0,15	Type	CUL 100/0,15
Electrical data	30		
	Operating data		
	current car. cap.		0.06 A
	Environment		
	Heat resistance		155 °C (CL.F)
	insulating varnish		min. Polyurethan, mod.
	Tin-plate		>350 °C
	Measures and weights		
	Wire diameter		0.15 mm
	Weight		0.10 kg
Length m (min.)		509	

Subjects to change.