


1/2" COMPOSITE COMPACT IMPACT WRENCH | NS.1500F2



Description

- Durable twin hammer mechanism encased in a strong aluminium housing.
- Low consumption yet powerful motor delivering 505 N.m of torque.
- Forward / reverse knob with integrated 3 power settings in forward.
- Swivel air inlet to avoid coiling of the hose.
- Durable and insulating composite housing, chemical and acid resistant.
- Feather teasing trigger for optimal speed regulation.
- Socket ring retainer for safety.
- Also available as a 3/8": NJ.2000F2.
- Breakaway torque 670 N.m.
- Breakaway torque 542 N.m.
- Blows per minute 1250 cpm.
- Free speed 9650 tr/min.
- Square drive 1/2".
- Working pressure 6,2 bar.
- Average air consumption 120 l/min.
- Air inlet 1/4".
- Minimum hose diameter 10 mm - 3/8".
- Vibration 8,20 m/s²/a.
- Vibration 1,55 m/s²/K.
- Sound pressure 92,90 dB(A).
- Sound power 103,90 dB(A).

Information

H [mm]	165
L [mm]	157
L1 [mm]	58
[kg]	1,300