

Features

- A manual depaneling tool designed to separate PCBs in a quick, economic and safe way, obtaining well-finished cut surfaces; the maximum length of the isthmus (tab) should not exceed 3mm.
- Blade size 2.3mm (0.090")
- Maximum PCB thickness 1.6mm.
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- ESD safe version.
- Laser marking.
- Made in Italy.

RS PRO ESD PCB separator pliers (blade thickness 2.3mm-0.090")

RS Stock No.: (0429769)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Made in Italy with a high carbon steel and undergo a controlled atmosphere heat treatment.
- The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.
- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.
- A manual depaneling tool designed to separate PCBs in a quick, economic and safe way, obtaining well-finished cut surfaces; the maximum length of the isthmus (tab) should not exceed 3 mm.
- Blade size 2.3mm (0.090")
- Maximum PCB thickness 1.6mm
- Minimum isthmus distance 11mm
- Maximum cutting force 7kg

General Specifications

Blade size	2.3mm – 0.090"
Blade length	11 mm +/-5 mm
Maximum PCB thickness	1.6 mm
Max isthmus (tab) length	3 mm
Minimum isthmus (tab) distance	11 mm
Maximum cutting force	7 kg
Material	High Carbon Steel
Finish	Anti-reflection phosphating surface treatment, grey grip
ESD Safe	Yes. Standard IEC 61340-5-1

Mechanical Specifications

Overall Length	147 mm
Weight	90 g

