- Power, data / signal, hybrid
- IP68 mated or unmated
- Blind mating with audible feedback
- Compact design
- Flammability UL 94V-0
- UV resistant

Amphenol LTW

HS-Lok Connector

Push pull quick mating



Unrivaled InterConnects for Harsh Environments



Production Sites (Taiwan, China, Mexico)

30+ **Market Applications** 90,000+

Products

Since 1993, Amphenol LTW Technology "ALTW" lives and breathes to create, innovate, design and produce "unrivaled interconnects for harsh environments". With over 300 worldwide patents, not only does ALTW offer the broadest and widest range of rugged interconnects in the industry but also customization with the mission of "Customer Satisfaction First". Undoubtedly, ALTW is the leader in rugged interconnects, highly recognized for its uncompromising quality, short lead time, fast and tailored service and its very competitive pricing.

Regardless of the challenging environments that your products will be subject to; there is a very good chance that you will find what you are looking for with ALTW.


HS-Lok Connector

Amphenol LTW's HS-Lok Push-Lock connectors provide you a simple quick and safe release to save you time and cost, with just a small pull force. HS-Lok offers IP68 waterproof protection and UL-F1 UV resistance, making them ideal for indoor or outdoor wet locations and space-constraint applications. In addition, the audible feedback and guided key design ensuring error-proof and easy assembly for blind mating.

Our HS-Lok connectors are UL2238 compliant and rated up to 5A for low voltage power and data transmissions, available in 2 to 6 contacts and hybrid (Power + Data) options to suit users variable requirements.

- Flammability UL 94V-0 & UV resistant
- UL2238 certified
- RoHS & REACH compliant






Accessory (click the image to find more product information)

Waterproof Cap







Size	Waterproof Cap	Mating Pair (Gender)	P/N
Q8	Cap only	FEMALE	CAP-WBBFQCA1
Q8	Cap only	MALE	CAP-WBBMQMA1
Q8	With fish line	MALE	CAP-WBBMQMD1

Product Range Overview

SUB SERIES	Q8	
Mating Style	Push Pull	
Plastic Version	✓	
Metal Version	-	
No. of Contacts	2 ~ 6	
Plating of Contacts	Gold Plated	
Operating Voltage (AC/DC)	100V DC, 300V, 300V AC / 100V DC	
Nominal Current	2A, 5A, 5A+2A	
Operating Temperature	Receptacle: -40°C ~ 105°C Overmolded With Cable: -40°C ~ 105°C Field Serviceable/Installable: -40°C ~ 105°C	
Fasten Style of Nut	Front	
Receptacle	✓	
Receptacle with Cable	-	
Field Serviceable/Installable	✓	
Overmolded with Cable	✓	
Accessories	✓	
Mating Cycles (Pin Contact)	2000	
IP Rating	IP68	
Salt Spray (Connector, Mated)	500h	
UV Resistant	✓	
Flammability Rating	UL94V-0	
Vibration Resistant	Frequency Range 10 ~ 55Hz / Amplitude 1.52mm	
RoHS Compliant	✓	
REACH Compliant	✓	
Certifications	UL2238	
Applicable Wire Gauge	24 ~ 20AWG	

Served Markets & Applications

Market	Application		
LED Lighting	 Architectural Lighting Residential, Medical, and Commercial Lighting Street, Parking lot, and Park Lighting Entertainment and Signage Lighting 	 Horticulture, Grow, & Warehouse Lighting Mass Transportation and Vehicles Marine Vessel Lighting Appliances and Equipment Lighting 	
Marine	Navigation System: Radar, GPS, Sailing Instruments, Chart Plotter Communication: Radio, AIS Instrumentation & Monitoring: MFD, CCTV, Sensors	 Power Distribution: Appliances, Charging, HVAC Entertainment: Video, Audio, Decorative Motors: Outboard, Inboard, Pump, Actuator, Trolling 	
Broadband Wireless Access	Access Point: LTE, 5G Cellular, Subscriber, and Mobile Station Wireless Router and Mobile Backhaul	Power Supply and Distribution System Other Communication Equipment	
Industrial Automation	 Motors: Servo, Step, Encoder, Actuator Power Supply and Distribution Robotic Arms, Packaging, and Conveyor System 	 Controller: Machine Vision, AVI, Sensors Autonomous Robots, Forklifts Industrial PC, Counters, and Display 	
Renewable Energy	Energy Storage and Portable Energy		
Heavy Equipment	Navigation System: GPS, Lidar, Radar, Ultrasonic Instrumentation, Control, and Diagnostic Systems Monitoring: Display, Camera, Imaging	Safety System: Sensor, ADAS, Telematics & Tracking Communication and Electronic Toll Systems Power Distribution: Charging, Lighting, Equipment	
Autometer	Metering: Water, Electric, & Gas Meter Power and Control: Drone, Security Alarm	Monitoring: Sewage, Telemetry, and Vehicle Tracking	
Test Equipment	 Measuring Device: Air, Humidity, Light, Sound, Water, Image, Weight, Height Detectors: Gas, Fire, Leak, Motion, Heat Monitoring: Seismic (earthquake), Climatic 	Weighing: Weigh, In-motion Geodetic System: Surveying, Laser Marking, Borrescope	
Hybrid Electric Vehicles	Motor Module: Scooter, Hoover board, Wheelchair Sensors: Speedometer, Fuel, Cleaning	Device Communication: CAN, In-vehicle Info Lighting: Interior and Exterior LED	
Railway Mass Transit	Navigation: GPS, Radar, Lidar, Ultrasonic HVAC Infotainment: Display, Sound, Broadcasting, Monitor	 Sensors: Speedometer, Fuel, Cleaning Communication: Main Controller, In-vehicle Info Lighting: Interior and Exterior 	
Mobile Devices	Drone Remote Controller Measurement: Altimeter, Gesture, Piezoelectric	Handheld: Barcode, Scanner, Portable lamp, GPS	
Transpo	Monitoring: Display, CCTV, Lidar, Surveillance Cam Navigation: GPS, Radar		
Medical Equipment	Patient Care: Electric Beds, Wheelchair Lift & Stair, Rehabilitation System, Mobile Carts		
Automotive Diagnostics	Auto-crash Detection & Notification System Vehicle Tracking and Roadside Assistance System	Remote Diagnostics	
UAV	Drone: Commercial, Consumer, & Military		
Lifts & Materials Handling	Forklift, Industrial Lift, Material Handling		
Remote Video Response Center	Monitoring: Display ,CCTV, Dome, IP Camera Detection: Auto-License Plate Recognition, Alarm Identification: Fingerprint, Face Detection, Encoders	 Remote Control Devices and Sensors Peripherals: Junction Boxes and Cabling System Lighting: Interior and Exterior 	
Autonomous	Navigation & Sensor: GPS, Lidar, Radar, Ultrasonic, IMU Imaging: Cameras, Monitors, Infotainment Display	Controller: Inertial Measurement Unit & Navigation System, Central Computer	
Rugged IT	Telemetry Military Notebook & Tablet and VR & AR	Night Vision Googles and Camera Communication Equipment	



Contact Us

Luc Kan | Sales & Marketing | luc@ltw-tech.com Customer Service | sales@ltw-tech.com

Follow Us







