


## FEATURES

- **Abrasion Resistant:** Provides durability in high-wear environments
- **Chemical Resistant:** Suitable for use with various chemicals without degradation
- **Moisture Resistant:** Maintains performance in humid conditions
- **Maximum Operating Pressure of 26 bar:** Ensures safe operation under high pressure
- **Wide Temperature Range (-30 °C to 60 °C):** Suitable for diverse environmental conditions
- **Nylon 12 Material:** Offers flexibility and strength
- **Blue Colour:** Easy identification and aesthetic integration

## RS PRO 2.5 mm Flexible Tubing, Nylon 12

RS Stock No: 631-938



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO flexible tubing is designed for a variety of industrial applications, offering excellent performance in demanding environments. Made from durable Nylon 12, it is ideal for use in air brake systems, food production lines, and more. Its abrasion, chemical, and moisture resistance ensures longevity and reliability.

### General Specifications

Application	Air Brake, Food Production Line, Fuel, Lubrication, Pneumatic
Colour	Blue
Material	Nylon 12
Maximum Operating Pressure	26 bar
Number of Tubes	1
Product Type	Flexible Tubing
Resistance Features	Abrasion Resistant, Chemical Resistant, Moisture Resistant

### Mechanical Specifications

Inside Diameter	2.5 mm
Length	30 m
Outside Diameter	4 mm

### Operation Environment Specifications

Maximum Operating Temperature	60 °C
Minimum Operating Temperature	-30 °C

### Approvals

Standards/Approvals	BS 5409, DIN 73378, DIN 74324, ISO 7628, RoHS 3
---------------------	---