




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Insulation Boots & Sleeves



Insulation Boot & Sleeve Product Type: **Insulation Sleeve**

Terminal Orientation: **Straight**

Primary Product Material: **PVC**

Primary Product Color: **Blue**

Packaging Method: **Bag**

Features

Product Type Features

Insulation Boot & Sleeve Product Type	Insulation Sleeve
---------------------------------------	-------------------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Material	PVC
Primary Product Color	Blue

Contact Features

Accepts Terminal Style	Receptacle
Terminal Orientation	Straight

Dimensions

Product Length	26 mm[1.02 in]
----------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

--	--



Packaging Quantity	1000
Packaging Method	Bag

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(177)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(5)



[Quick Disconnects\(173\)](#)


Customers Also Bought



TE Part #175023-1
[PL 250 RECEPTACLE 18-14 AWG PTBR](#)



TE Part #160743-4
[110 FASTIN FASTON, TAB, 20-16 AWG, PTBR](#)



TE Part #170014-6
[FF 110 TAB 20-16AWG PTBR](#)



TE Part #62131-3
[CLSTR PIN RCPT](#)




TE Part #316834-2
[040 SEALED TAB CONT. S / GOLD](#)



TE Part #CAT-D9934-A75F
[DYNAMIC 3200 HDR ASSY](#)



TE Part #1217825-1
[FLUORESCENT TUBE SOCKET TERMINAL](#)



TE Part #172774-4
[MIC MK-II LP](#)

Documents

Product Drawings

[POSITIVE LOCK 250 \(6.3 MM\) SLEEVE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_174817-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_174817-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_174817-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Instruction Sheets

Instruction Sheet (non U.S.)

English

POSITIVE LOCK EX CONTACT

English

Agency Approvals

UL Report

English