



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Between Series Adapter**

Body Orientation: **Straight**

Side A Interface: **SMA**

Side A Gender: **Plug**

Side B Interface: **BNC**

Features

Product Type Features

Connector Interface Adapter Type	Between Series Adapter
Side A Interface	SMA
Side A Gender	Plug
Side B Interface	BNC
Side B Gender	Jack
Connector System	Wire-to-Wire
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Body Material	Brass, Stainless Steel
Seal Material	Silicone Rubber



Contact Features

RF Connector Center Contact Material	Beryllium Copper
RF Connector Center Contact Plating Material	Gold (Au)

Mechanical Attachment

Mounting Feature Material	Stainless Steel
Connector Mounting Type	Panel Mount

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	4 GHz
Circuit Application	Power & Signal

Other

Dielectric Material	TFE Fluorocarbon
---------------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as




EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1588908-1
PRO BEAM JR, FRRL KIT, PC 126
SEALED




TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R




TE Part #2102061-3
Mezalok, Socket, 114 p, 12 mm, 50 Au,
TL




TE Part #234064-E
STVBTL BUT 100 CSI 2026 207 * J 2
34093




TE Part #352171-1
Z-PACK/B F-HDR. 95P




TE Part #1054869-1
2084 0000 02




TE Part #52928-1
PIDG SP SPD 22-16COM22-18MIL 5



TE Part #1-2000713-3
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #2-1419106-6
27E894=SOCKET,KH,14,SCW,POLY,
DINRAIL



TE Part #1-2000676-2
KEYED GUIDE PIN, MACHINED,
MULTIGIG,19MM

Documents

Product Drawings

3282 2241 00

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1058083-1_B.2d_dxf.zip

1058083-1

Between Series Adapter, Straight, SMA Side A, Plug Side A, BNC Side B, Jack Side B,
1 Position



English

Customer View Model

[ENG_CVM_CVM_1058083-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1058083-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RF Between Series Adapters](#)

English