



The Professional's Choice

SAFETY DATA SHEET

1. IDENTIFICATION OF THE MATERIAL AND SUPPLIER

1.1 Product identifier

Product name PERMA-MEND REPAIR PATCH
Synonyms 14089, 14094, 14096 - PRODUCT CODES • CRC PERMA-MEND REPAIR PATCH

1.2 Uses and uses advised against

Uses FIBREGLASS REPAIR • REPAIR AGENT

1.3 Details of the supplier of the product

Supplier name CRC INDUSTRIES (AUST) PTY LIMITED
Address 9 Gladstone Road, Castle Hill, NSW, 2154, AUSTRALIA
Telephone (02) 9849 6700
Fax (02) 9680 4914
Email info.au@crcind.com
Website www.crcindustries.com.au

1.4 Emergency telephone numbers

Emergency 13 11 26 (PIC)

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

CLASSIFIED AS HAZARDOUS ACCORDING TO SAFE WORK AUSTRALIA CRITERIA

Physical Hazards

Not classified as a Physical Hazard

Health Hazards

Skin Sensitisation: Category 1
Serious Eye Damage / Eye Irritation: Category 2B
Respiratory Sensitisation: Category 1
Carcinogenicity: Category 2

Environmental Hazards

Not classified as an Environmental Hazard

2.2 GHS Label elements

Signal word DANGER

Pictograms



Hazard statements

H317 May cause an allergic skin reaction.
H320 Causes eye irritation.
H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H351 Suspected of causing cancer.

PRODUCT NAME PERMA-MEND REPAIR PATCH

Prevention statements

P202	Do not handle until all safety precautions have been read and understood.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P264	Wash thoroughly after handling.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P285	In case of inadequate ventilation wear respiratory protection.

Response statements

P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P341	IF INHALED: If breathing is difficult, remove to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308 + P313	IF exposed or concerned: Get medical advice/ attention.
P321	Specific treatment is advised - see first aid instructions.
P363	Wash contaminated clothing before reuse.

Storage statements

P405	Store locked up.
------	------------------

Disposal statements

P501	Dispose of contents/container in accordance with relevant regulations.
------	--

2.3 Other hazards

No information provided.

3. COMPOSITION/ INFORMATION ON INGREDIENTS

3.1 Substances / Mixtures

Ingredient	CAS Number	EC Number	Content
NON HAZARDOUS INGREDIENTS	Not Available	Not Available	Remainder
STYRENE	100-42-5	202-851-5	<1%
MINERAL FILLER(S)	-	-	20 to 30%
POLYESTER RESIN(S)	-	-	20 to 30%

4. FIRST AID MEASURES

4.1 Description of first aid measures

Eye	Exposure is considered unlikely.
Inhalation	Due to product form / nature of use, an inhalation hazard is not anticipated.
Skin	If skin or hair contact occurs, remove contaminated clothing and flush skin and hair with running water.
Ingestion	For advice, contact a Poisons Information Centre on 13 11 26 (Australia Wide) or a doctor (at once). Due to product form and application, ingestion is considered unlikely.
First aid facilities	None allocated.

4.2 Most important symptoms and effects, both acute and delayed

Irritating to eyes. May cause sensitisation by inhalation and skin contact. Suspected of causing cancer.

4.3 Immediate medical attention and special treatment needed

Treat symptomatically.

5. FIRE FIGHTING MEASURES

5.1 Extinguishing media

Use an extinguishing agent suitable for the surrounding fire.

5.2 Special hazards arising from the substance or mixture

Non flammable. May evolve carbon oxides and hydrocarbons when heated to decomposition.

PRODUCT NAME PERMA-MEND REPAIR PATCH

5.3 Advice for firefighters

Treat as per requirements for surrounding fires. Evacuate area and contact emergency services. Remain upwind and notify those downwind of hazard. Wear full protective equipment including Self Contained Breathing Apparatus (SCBA) when combating fire. Use waterfog to cool intact containers and nearby storage areas.

5.4 Hazchem code

None allocated.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Wear Personal Protective Equipment (PPE) as detailed in section 8 of the SDS.

6.2 Environmental precautions

Prevent product from entering drains and waterways.

6.3 Methods of cleaning up

If spilt, collect and reuse where possible.

6.4 Reference to other sections

See Sections 8 and 13 for exposure controls and disposal.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

7.2 Conditions for safe storage, including any incompatibilities

Store in a cool, dry area. Ensure containers are tightly sealed, adequately labelled and protected from physical damage.

7.3 Specific end uses

No information provided.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

8.1 Control parameters

Exposure standards

Ingredient	Reference	TWA		STEL	
		ppm	mg/m ³	ppm	mg/m ³
Styrene, monomer	SWA [AUS]	50	213	100	426

Biological limits

Ingredient	Determinant	Sampling Time	BEI
STYRENE	Mandelic acid plus phenylglyoxylic acid in urine	End of shift	400 mg/g creatinine
	Styrene in urine	End of shift	40 µg/L

Reference: ACGIH Biological Exposure Indices

8.2 Exposure controls

Engineering controls Avoid inhalation. Use in well ventilated areas. Maintain dust / fume levels below the recommended exposure standard.

PPE

Eye / Face	When using large quantities or where heavy contamination is likely, wear safety glasses.
Hands	When using large quantities or where heavy contamination is likely, wear viton® gloves.
Body	Not required under normal conditions of use.
Respiratory	At high vapour levels, wear a Type A (Organic vapour) respirator.

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	GREY SOLID PATCH
Odour	STYRENE ODOUR
Flammability	NON FLAMMABLE
Flash point	NOT AVAILABLE
Boiling point	NOT AVAILABLE
Melting point	NOT AVAILABLE
Evaporation rate	NOT AVAILABLE
pH	NOT AVAILABLE
Vapour density	NOT AVAILABLE
Specific gravity	NOT AVAILABLE
Solubility (water)	INSOLUBLE
Vapour pressure	NOT AVAILABLE
Upper explosion limit	NOT RELEVANT
Lower explosion limit	NOT RELEVANT
Partition coefficient	NOT AVAILABLE
Autoignition temperature	NOT AVAILABLE
Decomposition temperature	NOT AVAILABLE
Viscosity	NOT AVAILABLE
Explosive properties	NOT AVAILABLE
Oxidising properties	NOT AVAILABLE
Odour threshold	NOT AVAILABLE

10. STABILITY AND REACTIVITY

10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

10.2 Chemical stability

Stable under recommended conditions of storage.

10.3 Possibility of hazardous reactions

Polymerization is not expected to occur.

10.4 Conditions to avoid

Avoid heat, sparks, open flames and other ignition sources.

10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites).

10.6 Hazardous decomposition products

May evolve carbon oxides and hydrocarbons when heated to decomposition.

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Information available for the ingredients:

Ingredient	Oral LD50	Dermal LD50	Inhalation LC50
STYRENE	> 2000 mg/kg (rat)	> 2000 mg/kg (rat) (OECD 402)	11.8 mg/L/4 hours (rat) (vapour)

Skin Contact may result in irritation, redness, rash and dermatitis.

Eye Contact may result in irritation, lacrimation, pain and redness.

Sensitisation May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled.

Mutagenicity Not classified as a mutagen.

Carcinogenicity Styrene is classified as possibly carcinogenic to humans (IARC Group 2B).

PRODUCT NAME PERMA-MEND REPAIR PATCH

Reproductive	Not classified as a reproductive toxin.
STOT - single exposure	Not classified as causing organ damage from single exposure.
STOT - repeated exposure	Not classified as causing organ damage from repeated exposure.
Aspiration	Not classified as causing aspiration.

12. ECOLOGICAL INFORMATION

12.1 Toxicity

No information provided.

12.2 Persistence and degradability

No information provided.

12.3 Bioaccumulative potential

No information provided.

12.4 Mobility in soil

No information provided.

12.5 Other adverse effects

No information provided.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods**Waste disposal** Dispose of to an approved landfill or waste processing site. Contact the manufacturer/supplier for additional information (if required).**Legislation** Dispose of in accordance with relevant local legislation.

14. TRANSPORT INFORMATION

NOT CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE, IMDG OR IATA

	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
14.1 UN Number	None allocated.	None allocated.	None allocated.
14.2 Proper Shipping Name	None allocated.	None allocated.	None allocated.
14.3 Transport hazard class	None allocated.	None allocated.	None allocated.
14.4 Packing Group	None allocated.	None allocated.	None allocated.

14.5 Environmental hazards

No information provided.

14.6 Special precautions for user**Hazchem code** None allocated.

15. REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**Poison schedule** Classified as a Schedule 5 (S5) Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).**Classifications** Safework Australia criteria is based on the Globally Harmonised System (GHS) of Classification and Labelling of Chemicals.**Inventory listings** **AUSTRALIA: AIIC (Australian Inventory of Industrial Chemicals)**
All components are listed on AIIC, or are exempt.

16. OTHER INFORMATION

Additional information

PERSONAL PROTECTIVE EQUIPMENT GUIDELINES:

The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as form of product, method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.

HEALTH EFFECTS FROM EXPOSURE:

It should be noted that the effects from exposure to this product will depend on several factors including: form of product; frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.

Abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds
CNS	Central Nervous System
EC No.	EC No - European Community Number
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)
GHS	Globally Harmonized System
GTEPG	Group Text Emergency Procedure Guide
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration, 50% / Median Lethal Concentration
LD50	Lethal Dose, 50% / Median Lethal Dose
mg/m ³	Milligrams per Cubic Metre
OEL	Occupational Exposure Limit
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).
ppm	Parts Per Million
STEL	Short-Term Exposure Limit
STOT-RE	Specific target organ toxicity (repeated exposure)
STOT-SE	Specific target organ toxicity (single exposure)
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons
SWA	Safe Work Australia
TLV	Threshold Limit Value
TWA	Time Weighted Average

Report status

This document has been compiled by RMT on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It is based on information concerning the product which has been provided to RMT by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

While RMT has taken all due care to include accurate and up-to-date information in this SDS, it does not provide any warranty as to accuracy or completeness. As far as lawfully possible, RMT accepts no liability for any loss, injury or damage (including consequential loss) which may be suffered or incurred by any person as a consequence of their reliance on the information contained in this SDS.

Prepared by

Risk Management Technologies
 5 Ventnor Ave, West Perth
 Western Australia 6005
 Phone: +61 8 9322 1711
 Fax: +61 8 9322 1794
 Email: info@rmt.com.au
 Web: www.rmtglobal.com

[End of SDS]