



Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A**

USB Version: **2.0**

Connector Profile: **Standard**

Connector & Housing Type: **Plug**

Number of Ports: **1**

Features

Product Type Features

USB Adapter Type	A
USB Version	2.0
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
USB Connector Type	USB 2.0 Type-A

Configuration Features

Number of Ports	1
Number of Positions	4

Body Features

Shell Plating Material	Nickel
Connector Profile	Standard

Contact Features



Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Current Rating (Max)	1.5 A

Mechanical Attachment

Locking Feature	With
PCB Mount Location	Cable Mount
PCB Mount Retention Type	None
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	Black
Housing Material	Polyester GF
Body Orientation	Straight

Usage Conditions

Soldering Temperature (Max)	350 °C[662 °F]
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Assembly Process Feature	None
Circuit Application	Power, Signal & High Speed Data

Industry Standards

Industry Standard	USB 2.0
IP Rating	IP67

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224)



Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1954643-1
Recpt Kit, Series A to Series A



TE Part # 1828740-1
ASSEMBLY, PROTECTIVE CAP

Also in the Series | Industrial USB IP20




USB Connectors(9)



USB Mini Connectors(1)



USB Type A Connectors(8)



USB Type B Connectors(1)

Customers Also Bought



TE Part #YDTS26W11-98SEV001
PLUG ASSY



TE Part #322798
SOLIS R HR 22-16COM 22-18MIL 8



TE Part #ZPF000000000015303
DMC-M 20-22 PB




TE Part #369276-000
S1184-KIT-1



TE Part #F97579-000
CP-101635-2.5-X




TE Part #608036-4
SILICONE FUSION TAPE, 1"X36'



TE Part #218696-001
22759/43-20-9



TE Part #5070102034
RNF-100-1-X-STK



TE Part #216112-002
22759/32-22-9



TE Part #916601-000
55PC6015-24-9-9CS2573

Documents

Product Drawings
Plug Kit,USB Series A

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1954637-1_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1954637-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1954637-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773463-4_INDUSTRIAL_USB_CONNECTORS

English

CONNECTIVITY SOLUTIONS FOR INFOTAINMENT APPLICATIONS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English