

Features

- Multifunction economy version of time relay for universal use in automation, control and regulation or in house installations.
- Universal supply voltage: AC 24 – 240 V (AC 50/60 Hz) and DC 24 V.
- Comfortable and well-arranged function and time-range setting by rotary switches.
- Time scale 0.1 s - 10 hrs divided into 6 ranges:
- (0.1 s - 1 s / 1 s - 10 s / 0.1 min - 1 min / 1 min - 10 min / 0.1 hrs - 1 h / 1 h - 10 hrs).
- Output contact: 1x changeover/SPDT 8 A.
- Multifunction red LED flashes or shines depending on the operating status.

RS PRO Timer Relay

800993



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product description

- Multifunction economy version of time relay for universal use in automation, control and regulation or in house installations.
- Universal supply voltage: AC 24 – 240 V (AC 50/60 Hz) and DC 24 V.
- Comfortable and well-arranged function and time-range setting by rotary switches.
- Time scale 0.1 s - 10 hrs divided into 6 ranges:
(0.1 s - 1 s / 1 s - 10 s / 0.1 min - 1 min / 1 min - 10 min / 0.1 hrs - 1 h / 1 h - 10 hrs).
- Output contact: 1x changeover/SPDT 8 A.
- Multifunction red LED flashes or shines depending on the operating status.

Power supply

Supply terminals:	A1-A2
Supply voltage:	AC 24 - 240 V DC 24 V (AC 50-60 Hz)
Consumption (max.):	2 VA/1.5 W
Supply voltage tolerance:	-15 %; +10 %

Time circuit

Number of functions:	6
Time ranges:	0.1 s - 10 h
Time setting:	rotary switch and potentiometer
Time deviation:	5 % - mechanical setting
Repeat accuracy:	0.2 % - set value stability
Temperature coefficient:	0.01 %/°C, at = 20 °C (0.01 %/°F, at = 68 °F)

Output

Contact type:	1x changeover/SPDT (AgNi)
Current rating:	8 A/AC1; PD. B300
Breaking capacity:	2000 VA/AC1, 192 W/DC
Switching voltage:	AC 250 V/DC 24 V
Power dissipation (max.):	0.6 W
Mechanical life:	10.000.000. ops.
Electrical life (AC1):	100.000 ops.


Control

Control terminals:	A1-S
Load between S-A2:	Yes
Impulse length:	min. 25 ms/max. unlimited
Reset time:	max. 150 ms

Other information


Operating temperature:	-20 .. +55 °C (-4 .. 131 °F)
Storage temperature:	-30 .. +70 °C (-22 .. 158 °F)
Dielectric strength:	AC 4 kV (supply – output)
Operating position:	any
Mounting:	DIN rail EN 60715
Protection degree:	IP40 front panel/IP20 terminals
Overvoltage category:	III.
Pollution degree:	2
Max. cable size (mm ²):	solid wire max. 1x 2.5 or 2x 1.5/ with sleeve max. 1x 2.5 (AWG 12)
Dimensions:	90 × 17.6 × 64 mm (3.5" × 0.7" × 2.5")
Weight:	62 g (2.2 oz)
Standards:	EN 61812-1

Approvals




1. Supply terminals
2. Control input „S“
3. Supply indication
4. Fine time setting
5. Output contact
6. Output indication
7. Time setting
8. Function setting

Connection




Possibility to connect load onto controlling input

It is possible to connect the load (e.g.: contactor) between terminals S-A2, without any interruption of correct relay function.




Indication of operating states


Function a)



Function e)



Function



ON DELAY



OFF DELAY



INTERVAL ON



MEMORY LATCH with Delay



FLASHER - ON first



ON DELAY with Control Signal