


DATA SHEET O-Ring 104503

PART INFORMATION

Part number	104503
Inside diameter d1	4,20 mm
Cross-section d2	1,90 mm
Size standard	R3
Tolerance range according to	ISO 3601-1
Rubber family	NBR
Rubber compound	PC851
Quality acceptance criteria on aspect	ISO 3601-3



PC851 COMPOUND NFORMATION

Original characteristics

Hardness Sh A Tensile strength Elongation at break Compression set TR10 Brittle point Operational temperature range * Peak temperature

Rubber color

Official agreements Gaz : EN549 – H3B1 80 17 MPa 225 % 15 % (24h 100°C) -25 °C -35 °C -30 °C / 100 °C 120 °C

Black

NBR FAMILY

Good resistance

Mineral oils Domestic gas Water up to 70 °C Fuels Aliphatic solvants

Poor resistance Acids Atmospheric agents Brake fluids

Particularities Good mechanical characteristics

Typical applications Hydraulic & pneumatic Valves & fittings water and mineral gas Mineral oil & fuel circuits

* The temperature range is given as an indication and can be influenced by the environment, the fluids in contact and the operating conditions.



LE JOINT FRANCAIS SNC 1 rue Gutenberg ZI Ouest de Bazouges - 53200 CHATEAU-GONTIER - FRANCE www.oring.hutchinson.fr_- oring@hutchinson.com We make it **possible**