


# TIMKEN

The Timken Company  
 4500 Mt Pleasant St. NW  
 N. Canton, OH 44720  
 Phone: (234) 262-3000  
 E-Mail: [CustomerCAD@timken.com](mailto:CustomerCAD@timken.com) • Web site: [www.timken.com](http://www.timken.com)

## Timken Part Number 36690 - 36620, Tapered Roller Bearings - TS (Tapered Single) Imperial

This is the most basic and most widely used type of tapered roller bearing. It consists of two main separable parts: the cone (inner ring) assembly and the cup (outer ring). It is typically mounted in opposing pairs on a shaft.



[Specifications](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

### Specifications

<b>Series</b>	36600
<b>Cone Part Number</b>	36690
<b>Cup Part Number</b>	36620
<b>Design Units</b>	Imperial
<b>Bearing Weight</b>	2.300 Kg 5.00 lb
<b>Cage Type</b>	Stamped Steel

### Dimensions

<b>d - Bore</b>	146.050 mm 5.7500 in
<b>D - Cup Outer Diameter</b>	193.675 mm 7.6250 in

<b>B - Cone Width</b>	28.575 mm 1.1250 in
<b>C - Cup Width</b>	23.020 mm 0.9063 in
<b>T - Bearing Width</b>	28.575 mm 1.1250 in

#### Abutment and Fillet Dimensions

<b>R - Cone Backface "To Clear" Radius<sup>1</sup></b>	1.520 mm 0.06 in
<b>r - Cup Backface "To Clear" Radius<sup>2</sup></b>	1.52 mm 0.06 in
<b>da - Cone Frontface Backing Diameter</b>	152.91 mm 6.89 in
<b>db - Cone Backface Backing Diameter</b>	154.94 mm 6.10 in
<b>Da - Cup Frontface Backing Diameter</b>	188.00 mm 7.41 in
<b>Db - Cup Backface Backing Diameter</b>	182.12 mm 7.17 in
<b>Ab - Cage-Cone Frontface Clearance</b>	3.3 mm 0.13 in
<b>Aa - Cage-Cone Backface Clearance</b>	1 mm 0.04 in
<b>a - Effective Center Location<sup>3</sup></b>	4.80 mm 0.19 in

#### Basic Load Ratings

<b>C90 - Dynamic Radial Rating (90 million revolutions)<sup>4</sup></b>	50900 N 11400 lbf
<b>C1 - Dynamic Radial Rating (1 million revolutions)<sup>5</sup></b>	196000 N 44200 lbf
<b>C0 - Static Radial Rating</b>	394000 N 88600 lbf
<b>C<sub>a90</sub> - Dynamic Thrust Rating (90 million revolutions)<sup>6</sup></b>	32100 N 7220 lbf

## Factors

<b>K - Factor<sup>7</sup></b>	1.59
<b>e - ISO Factor<sup>8</sup></b>	0.37
<b>Y - ISO Factor<sup>9</sup></b>	1.63
<b>G1 - Heat Generation Factor (Roller-Raceway)</b>	366
<b>G2 - Heat Generation Factor (Rib-Roller End)</b>	121
<b>Cg - Geometry Factor</b>	0.177

<sup>1</sup> These maximum fillet radii will be cleared by the bearing corners.

<sup>2</sup> These maximum fillet radii will be cleared by the bearing corners.

<sup>3</sup> Negative value indicates effective center inside cone backface.

<sup>4</sup> Based on  $90 \times 10^6$  revolutions  $L_{10}$  life, for The Timken Company life calculation method.  $C_{90}$  and  $C_{a90}$  are radial and thrust values.


<sup>5</sup> Based on  $1 \times 10^6$  revolutions  $L_{10}$  life, for the ISO life calculation method.

<sup>6</sup> Based on  $90 \times 10^6$  revolutions  $L_{10}$  life, for The Timken Company life calculation method.  $C_{90}$  and  $C_{a90}$  are radial and thrust values for a single-row,  $C_{90(2)}$  is the two-row radial value.

<sup>7</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

<sup>8</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

<sup>9</sup> These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.



**IMPERIAL UNITS**

ISO Factor - e	0.37
ISO Factor - Y	1.63
Bearing Weight	5 lb
Number of Rollers Per Row	43
Effective Center Location	0.19 inch

**TIMKEN**®

**36690 - 36620**  
**TS BEARING ASSEMBLY**

**THE TIMKEN COMPANY**  
 NORTH CANTON, OHIO USA

K Factor	1.59
Dynamic Radial Rating - C90	50900 lbf
Dynamic Thrust Rating - Ca90	32100 lbf
Static Radial Rating - C0	394000 lbf
Dynamic Radial Rating - C1	196000 lbf

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

**FOR DISCUSSION ONLY**