



CSX-WBF114128AA10Z

CSS/CSX High Speed

COLOR SENSORS





Ordering information

Туре	Part no.
CSX-WBF114128AA10Z	1120183

Other models and accessories → www.sick.com/CSS_CSX_High_Speed

Illustration may differ



Detailed technical data

Features

Dimensions (W x H x D)	30 mm x 53 mm x 78.5 mm
Sensing distance	13 mm
Sensing distance tolerance	± 5 mm
Housing design	X housing
Light source	LED, RGB ¹⁾
LED risk group marking	1
Wave length	460 nm, 530 nm, 625 nm
Light emission	Long side of housing
Light spot size	2 mm x 4 mm
Light spot direction	Vertical ²⁾
Teach-in mode	Single value teach-in Multi value teach-in
Color mode	C (Color) C + I (Color + Illumination)
Output mode	4 colors in standard mode/best fit mode 15 colors in coded mode
Adjustment of the sensitivity	Continuous: 0 999
Available job banks	4
Output (channel)	4 x hardware switching outputs 24 x virtual switching outputs via IO-Link

 $^{^{1)}}$ Average service life: 100,000 h at T_U = +25 °C.

²⁾ In relation to long side of housing.

Parameter presettings

Pin 4 / pin 5: Preset configuration

Mechanics/electronics

Supply voltage	10.8 V DC 28.8 V DC ¹⁾
Ripple	≤ 5 V _{pp} ²⁾
Current consumption	$<$ 120 mA $^{3)}$
Switching frequency	13.8 kHz
Response time	36 μs
Jitter	18 μs
Switching output	Push-pull: PNP/NPN
Switching output (voltage)	Push-pull: PNP/NPN HIGH = U_V - 3 V/LOW \leq 3 V
Output current I _{max.}	100 mA ⁴⁾
Input, teach-in (ET)	Teach: $U = 10 \text{ V} < V_S$
Input, blanking input (AT)	Blanked: U = 10 V < Uv
Retention time (ET)	3 s, non-volatile memory
Connection type	Male connector M12, 8-pin
Protection class	III
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP67
Weight	94 g
Housing material	VISTAL®
Optics material	PMMA

 $^{^{1)}}$ Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %) . Operation in short-circuit protected network max. 8 A.

Communication interface

IO-Link	√ , IO-Link
VendorID	26
DeviceID HEX	80028E
DeviceID DEC	8389262
Process data structure	Bit 0 = switching signal Q_{L1} Bit 1 = empty Bit 2 = Quality of Run Alarm Bit 3 5 = Emission Color Bit 6 15 = Measurment Value Emission Color
Digital output	$Q_1 \dots Q_4$
Number	4
Digital input	ln_1 , ln_2
Number	2

 $^{^{1)}}$ Average service life: 100,000 h at TU = +25 °C.

²⁾ In relation to long side of housing.

 $^{^{2)}\,\}mbox{May}$ not fall below or exceed $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.

⁴⁾ Total current of all Outputs.

Ambient data

Ambient operating temperature	-20 °C +60 °C
Ambient temperature, storage	-25 °C +75 °C
Shock load	According to IEC 60068-2-27 (30 g/11 ms)
UL File No.	E181493

Connection type/pinouts


Connection type	Male connector M12, 8-pin
Pinouts	
WH 1	Q_{L1}/IN_1
BN 2	+ (L+)
GN 3	Q _{L1} /C
YE 4	Q_{L2}
GY 5	ln_2
PK 6	Q_{L3}
BU 7	- (M)
RD 8	Q_{L4}


Classifications


ECLASS 5.0	27270907
ECLASS 5.1.4	27270907
ECLASS 6.0	27270907
ECLASS 6.2	27270907
ECLASS 7.0	27270907
ECLASS 8.0	27270907
ECLASS 8.1	27270907
ECLASS 9.0	27270907
ECLASS 10.0	27270907
ECLASS 11.0	27270907
ECLASS 12.0	27270907
ETIM 5.0	EC001817
ETIM 6.0	EC001817
ETIM 7.0	EC001817
ETIM 8.0	EC001817
UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))

Dimensional drawing, sensor








- ① Optical axis
- ② Fixing hole
- 3 M12 male connector, delivery state
- ④ M12 male connector, end stop right
- ⑤ M12 male connector, end stop left
- Sensing distance
- ⑦ Display and adjustment elements

Pinouts

Pinouts, see table Technical data: Connection type/pinouts




Connector M12, 8-pin, A-coded

COLOR SENSORS

Adjustments

Display and adjustment elements



- ① LEDs (status display)
- ② 7-segment display
- ③ Plus/minus button

Recommended accessories

Other models and accessories → www.sick.com/CSS_CSX_High_Speed

	Brief description	Туре	Part no.
Universal bar clamp systems			
	Plate K for universal clamp bracket, steel, zinc coated, Universal clamp (2022726), mounting hardware	BEF-KHS-K01	2022718
	Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-A	4056054
	Mounting bar, L-shaped, 150 mm x 150 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-A	4056052
Others			
No.	 Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation 	YF2A18- 050UA5XLEAX	2095653

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

