

Eaton 102708

Catalog Number: 102708

Eaton xEnergy Basic LV systems Low voltage switchgear. Terminal block, 3 poles, 175A, 1 input-, 6 output terminals, ALU

General specifications



Product Name	Catalog Number
Eaton xEnergy Basic other accessory	102708
EAN	Product Length/Depth
4015081025688	43 mm
Product Height	Product Width
71 mm	80.1 mm
Product Weight	Compliances
0.4 kg	RoHS conform
Certifications	
IEC 60 947 -7 -1	

Product specifications

Special features

Clicks on DIN-rail or on base plate.

Save time on wiring.

Save 80% on space used.

Modular construction, 1-4 pole Systems can be built with several blocks.

Material, hexagon socket set screw: Steel

This power distribution block is suitable for ALU and CU conductors.

Please pay attention to the common handling guidelines when connecting the aluminium conductors.

Clean and brush the contact surfaces and lubricate them with an appropriate grease.

As precaution the connections should get retightened regularly.

Zinc plated (Hexagon socket set screw, Surface finish)

Functions

Additional equipment

Torque rating

6 Nm - 10 Nm / 53.1 lbf - 88.5 lbf (incoming). 3 Nm - 4 Nm / 26.5 lbf - 35.4 lbf (outgoing)

Conductor cross section (flexible, fine-strand) with cable end sleeve - max

70 mm²

Conductor cross section (flexible, fine-strand) with cable end sleeve - min

2.5 mm²

Conductor cross section (solid, solid-strand) - max

70 mm²

Conductor cross section (solid, solid-strand) - min

2.5 mm²

Amperage rating

175 A

Resources

Brochures

[eaton-xenergy-basic-light-brochure-br014024-en-us.pdf](#)

Catalogs

[eaton-distribution-boards-xenergy-basic-catalog-ca014010en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_BPZ-KB](#)

Drawings

[eaton-xenergy-basic-terminal-block-dimensions-022.eps](#)

Sales notes

[eaton-f3a-flange-flyer-fl019005en-en-us.pdf](#)

Rated short-time withstand current (I_{cw})

11 kA

Voltage rating at DC Cu (IEC) - max

1500 VDC

Number of poles

Three-pole

Degree of protection

IP20

Mounting position

Universal

Clamp material

Brass

Nickel plated

Comparative tracking index (CTI)

600 V

Housing material

PA66

Housing color

Light gray (RAL 7035)

Material

Aluminum

Mounting method

Floor standing distribution board

Flush mounting

Surface mounting

Flame classification (UL 94)

V-0

Heat deflection temperature

100 °C

Number of clamp positions per pole

7

Number of clamping units per pole

7

Rated peak withstand current

30 kA

Voltage rating at AC Al (IEC) - max

1000 VAC

Voltage rating at AC Cu (IEC) - max

1000 VAC

Voltage rating at DC Al (IEC) - max

1500 VDC

Rated operation current (Ie) Al (IEC)

125 A

Rated operation current (Ie) Cu (IEC)

175 A

Terminal capacity (single/multi-wire)

2.5 mm² - 16 mm² (outgoing)

16 mm² - 50 mm² (incoming, fine wire (with sleeve))

6 - 1 AWG (incoming, fine wire (with sleeve))

8 - 2/0 AWG (incoming)

14 - 8 AWG (outgoing, fine wire (with sleeve))

14 - 6 AWG (outgoing)

16 mm² - 70 mm² (incoming)

2.5 mm² - 10 mm² (outgoing, fine wire (with sleeve))



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia