

Bourdon tube pressure gauges, liquid filled,

Modelcode type: 213.53.0XX

Item number: 82169726

Description

| | |
|------------------|--------------|
| Design according | EN 837-1 |
| Accuracy class | class 1.6 |
| Scale range | -0.1...0 MPa |

Constructional design

| | |
|--------------------|-------------------------------|
| Process connection | M14 x 1,5 |
| Connector location | lower mount |
| Pressure element | Copper alloy |
| Movement | Copper alloy |
| Case | Crimp ring case (version 53) |
| Nominal size | 063 mm |
| Case filling fluid | glycerine |
| Pointer | plastic, black |
| Window | plastic, clear |
| Dial | plastic, white, with stop-pin |

Operating conditions

| | |
|---|---|
| Pressure limitation | Steady: 3/4 x full scale value Fluctuating: 2/3 x full scale value Short time: Full scale value |
| Permissible ambient temperature | -20 ... +60 °C |
| Permissible medium temperature | +60°C maximum |
| Temperature effect when the temperature deviates from the reference temperature (+20°C) | Max. +/-0.4 %/10 K of the span |
| Ingress protection | IP 65 |

Dial description:

| | |
|-----------------------------|--------|
| Pressure Gauge Standard | China |
| color for 1.scale (outside) | black |
| dial background | White |
| Manufacturer logo | *WIKA* |

Bourdon tube pressure gauges, liquid filled,

Modelcode type: 213.53.0XX

Item number: 82169726

| | |
|------------------------|------------|
| stop pin on dial | at zero |
| norm-mark on dial | *EN 837-1* |
| safetymark on dial | *S* |
| accuracy class on dial | *Cl.1.6* |

Labelcode

| | |
|-----------------------|---------------|
| Label | WIKA standard |
| language of the label | German |