


Connector Location A



Pin Connector Location A	Wire
1	CORE 1
2	CORE 2
3	CORE 3
4	CORE 4
5	CORE 5
6	CORE 6
7	CORE 7
8	CORE 8
9	CORE 9
10	CORE 10
	CORE 11 (N/C)
ITEM 60	G/Y

HARTING-prt.no	Length (L)	Cut Length
6630297002200	1000mm	1100mm
6630297002201	3000mm	3100mm
6630297002202	5000mm	5100mm

THIS CABLE REQUIRED THE FOLLOWING TESTS:
 CONTINUITY
 RESISTANCE
 HIGH VOLTAGE
 IN ACCORDANCE WITH SECTION 19 OF
 IPC/WHMA-A-620B

Pos.	Qty.	Part no.	Description
10	1	09330102602	Han 10E insert male crimp
20	10	09330006102	Han E M Crimp Contact Ag 2.5 mm / 14AWG
30	See Table	TBC	Cable - 12G 2.5mm O.D. 14.8mm
40	1	19000005190	Han CGM-P M25x1,5 D.9-16mm grey
50	1	19300101421	Han 10B-HTE-LC-4 Pegs-M25
60	1	6630CRI001700	BLUE M4 RING CRIMP RS267-3773 16-14 AWG
70	As req	TBC	Heatshrink

NOTE: CUT BACK CORE 11 AND COVER WITH HEATSHRINK

The transmission and reproduction of this drawing and the use and communication of its contents is prohibited unless specifically permitted. Offenders will be liable for damages. All rights in case of patent-, utility model- or design registration are reserved.	Customer identification RS		Project No. 66000P10		
	Material		Coating		
 All rights reserved Department HCS - UK	Created by PATELJ	Inspected by MOOREG	Standardisation CANHAM	Date 2018-07-10	State Approved
	Title HAN E - 10B CABLE -2.5MM2				Doc-Key / ECM-Nr. 100795247/UGD/000/A 500000137464
HARTING UK Limited NN4 7PW Northampton		Type CA	Number 663029700220XX		Rev. A Page 1/2

