SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Cleaner Professional

Creation date	03rd September 2025		
Revision date		Version	1.0

SECTION 1: Identification of the substance / mixture and of the company / undertaking

1.1. Product identifier

Product Name	RS PRO Cleaner Professional
Product Code(s)	802722, 802723
Substance / mixture	mixture
UFI	RVP1-N0TV-T00T-V27X

1.2. Relevant identified uses of the substance or mixture and uses advised against

Mixture's intended use

Cleaning agent.

Mixture uses advised against

The product should not be used in ways other than those referred in Section 1.

1.3. Details of the supplier of the safety data sheet

Supplier

RS Components Ltd
Birchington Road
Corby
Northants
NN17 9RS
Tel: +44 (0) 845 850 9900
RCustomerServicesUK@rs-components.com

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
Tel: +353 (0) 1 415 3100

Competent person responsible for the safety data sheet

Email	enquiries.ie@rs-components.com

1.4. Emergency telephone number

Tel: +44 (0) 1865 407333 (24hr)	+44 1235 239670 (24hr)
GB: N/A	IE: +353 (0)1 809 2166 (08:00 - 22:00)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification of the mixture in accordance with Regulation (EC) No 1272/2008

The mixture is classified as dangerous.

Aerosol 1, H222, H229
Skin Irrit. 2, H315
Eye Irrit. 2, H319
STOT SE 3, H336
Aquatic Chronic 2, H411

Most serious adverse physico-chemical effects

Pressurised container: May burst if heated. Extremely flammable aerosol.

Most serious adverse effects on human health and the environment

Causes skin irritation. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Hazard pictogram



Signal word

Danger

Hazardous substances

hydrocarbons, c7, n-alkanes, isoalkanes

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P260	Do not breathe dust/fume/gas/mist/vapours/spray.
P273	Avoid release to the environment.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P332+P313	If skin irritation occurs: Get medical advice/attention.
P410+P412	Protect from sunlight. Do no expose to temperatures exceeding 50 °C.
P501	Dispose of container to in accordance with local/regional/national/international regulations.

2.3. Other hazards

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605. Mixture does not contain any substance meet the criteria for PBT or vPvB in accordance with Annex XIII of Regulation (EC) No. 1907/2006 (REACH) as amended.

SECTION 3: Composition / information on ingredients

3.2. Mixtures

Mixture contains these hazardous substances and substances with the highest permissible concentration in the working environment

Identification numbers	Substance name	Content in % weight	Classification according to Regulation (EC) No 1272/2008	Note
EC: 927-510-4	hydrocarbons, c7, n-alkanes, isoalkanes	30	Flam. Liq. 2, H225 Asp. Tox. 1, H304 Skin Irrit. 2, H315 STOT SE 3, H336 Aquatic Chronic 2, H411	
Index: 601-003-00-5 CAS: 74-98-6 EC: 200-827-9	propane	<25	Press. Gas, Flam. Gas 1, H220	2
Index: 601-004-00-0 CAS: 106-97-8 EC: 203-448-7	butane	<25	Press. Gas, Flam. Gas 1, H220	1, 2
Index: 603-117-00-0 CAS: 67-63-0 EC: 200-661-7	propan-2-ol	<10	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336	
Index: 603-002-00-5 CAS: 64-17-5 EC: 200-578-6 Registration number: 01-2119457610-43	ethanol	<7	Flam. Liq. 2, H225 Eye Irrit. 2, H319 Specific concentration limit: Eye Irrit. 2, H319: C ≥ 50 %	

CAS: 109-87-5 EC: 203-714-2	dimethoxymethane	<7	Flam. Liq. 2, H225	

Notes

1 *Note C: Some organic substances may be marketed either in a specific isomeric form or as a mixture of several isomers. In this case the supplier must state on the label whether the substance is a specific isomer or a mixture of isomers.*

2 *Note U (Table 3): When put on the market gases have to be classified as "Gases under pressure", in one of the groups compressed gas, liquefied gas, refrigerated liquefied gas or dissolved gas. The group depends on the physical state in which the gas is packaged and therefore has to be assigned case by case. The following codes are assigned:*

Press. Gas (Comp.)
Press. Gas (Liq.)
Press. Gas (Ref. Liq.)
Press. Gas (Diss.)

Aerosols shall not be classified as gases under pressure (See Annex I, Part 2, Section 2.3.2.1, Note 2).

Full text of all classifications and hazard statements is given in the section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

If any health problems are manifested or if in doubt, inform a doctor and show him information from this safety data sheet.

If inhaled

Terminate the exposure immediately; move the affected person to fresh air. Protect the person against growing cold. Provide medical treatment if irritation, dyspnoea or other symptoms persist.

If on skin

Remove contaminated clothes. Wash the affected area with plenty of water, lukewarm if possible.

If in eyes

Rinse eyes immediately with a flow of running water, open the eyelids (also using force if needed); remove contact lenses immediately if worn by the affected person. Rinsing should continue at least for 10 minutes. Provide medical treatment, specialized if possible.

If swallowed

Unlikely.

4.2. Most important symptoms and effects, both acute and delayed

If inhaled

May cause drowsiness or dizziness.

If on skin

Causes skin irritation.

If in eyes

When intruding eyes, it can evoke irritation.

If swallowed

Irritation, nausea.

4.3. Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam, carbon dioxide, powder, water spray jet, water mist.

Unsuitable extinguishing media

Water - full jet.

5.2. Special hazards arising from the substance or mixture

In the event of fire, carbon monoxide, carbon dioxide and other toxic gases may arise. Inhalation of hazardous degradation (pyrolysis) products may cause serious health damage.

5.3. Advice for firefighters

Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely. Use a self-contained breathing apparatus and full-body protective clothing. Closed containers with the product near the fire should be cooled with water. Do not allow run-off of contaminated fire extinguishing material to enter drains or surface and ground water.

SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Cleaner Professional

Creation date	03rd September 2025		
Revision date		Version	1.0

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Provide sufficient ventilation. Pressurised container: May burst if heated. Extremely flammable aerosol. Remove all ignition sources. Use personal protective equipment for work. Follow the instructions in the Sections 7 and 8. Do not inhale gases and vapours. Prevent contact with skin and eyes.

6.2. Environmental precautions

Prevent contamination of the soil and entering surface or ground water. Do not allow to enter drains.

6.3. Methods and material for containment and cleaning up

Ventilate the room. In the event of leakage of the substantial amount of the product, inform fire brigade and other competent bodies. After removal of the product, wash the contaminated site with plenty of water.

6.4. Reference to other sections

See the Section 7, 8 and 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Prevent formation of gases and vapours in flammable or explosive concentrations and concentrations exceeding the occupational exposure limits. The product should be used only in the areas where it is not in contact with open fire and other ignition sources. Use non-sparking tools. Use of antistatic clothes and footwear is recommended. Do not inhale gases and vapours. Prevent contact with skin and eyes. No smoking. Protect against direct sunlight. Do not pierce or burn, even after use. Wash hands and exposed parts of the body thoroughly after handling. Do not spray on an open flame or other ignition source. Use only outdoors or in a well-ventilated area. Use personal protective equipment as per Section 8. Observe valid legal regulations on safety and health protection. Avoid release to the environment.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed containers in cold, dry and well ventilated areas designated for this purpose. Store locked up. Protect from sunlight. Keep container tightly closed. Do not expose to temperatures exceeding 50 °C.

7.3. Specific end use(s)

not available

SECTION 8: Exposure controls / personal protection

8.1. Control parameters

The mixture contains no substances for which occupational exposure limits are set..

8.2. Exposure controls

Take off contaminated clothing and wash before reuse. Follow the usual measures intended for health protection at work and especially for good ventilation. This can be achieved only by local suction or efficient general ventilation. If exposure limits cannot be observed in this mode, suitable protection of airways must be used. Do not eat, drink and smoke during work. Wash your hands thoroughly with water and soap after work and before breaks for a meal and rest.

Eye / face protection

Protective goggles.

Skin protection

Hand protection: Protective gloves resistant to the product. When choosing appropriate thickness, material and permeability of the gloves, observe recommendations of their particular manufacturer. Observe other recommendations of the manufacturer. Other protection: protective workwear. Contaminated skin should be washed thoroughly.

Respiratory protection

Halfmask with a filter against organic vapours or a self-contained breathing apparatus as appropriate if exposure limit values of substances are exceeded or in a poorly ventilated environment.

Thermal hazard

Data not available.

Environmental exposure controls

Observe usual measures for protection of the environment, see Section 6.2. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	gas

SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Cleaner Professional

Creation date	03rd September 2025		
Revision date		Version	1.0

Colour	data not available
Odour	characteristic
Melting point/freezing point	data not available
Boiling point or initial boiling point and boiling range	data not available
ethanol (CAS: 64-17-5)	-114 °C
Flammability	data not available
Lower and upper explosion limit	data not available
Flash point	data not available
ethanol (CAS: 64-17-5)	>17 °C
Auto-ignition temperature	data not available
Decomposition temperature	data not available
pH	data not available
ethanol (CAS: 64-17-5)	7 (>80% solution at 20 °C)
Kinematic viscosity	data not available
Solubility in water	data not available
Partition coefficient n-octanol/water (log value)	data not available
Vapour pressure	data not available
Density and/or relative density	data not available
Relative vapour density	data not available
Particle characteristics	data not available

9.2. Other information

not available

SAFETY DATA SHEET

according to Commission Regulation (EU) 2020/878 as amended

RS PRO Cleaner Professional

Creation date	03rd September 2025		
Revision date		Version	1.0

SECTION 10: Stability and reactivity

10.1. Reactivity

not available

10.2. Chemical stability

The product is stable under normal conditions.

10.3. Possibility of hazardous reactions

Unknown.

10.4. Conditions to avoid

The product is stable and no degradation occurs under normal use. Protect against flames, sparks, overheating and against frost. Pressurised container: May burst if heated.

10.5. Incompatible materials

Protect against strong acids, bases and oxidizing agents.

10.6. Hazardous decomposition products

Not developed under normal uses. Dangerous outcomes such as carbon monoxide and carbon dioxide are formed at high temperature and in fire.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Hazardous substances in concentrations exceeding exposure limits may cause acute inhalation poisoning, depending on the concentration and duration of exposure. No toxicological data is available for the mixture.

Acute toxicity
Data for the mixture are not available. Based on the available data, the criteria for classification of the mixture are not met.

ethanol					
Route of exposure	Parameter	Value	Exposure time	Species	Sex
Inhalation (vapor)	LC_{50}	124.7 mg/l	4 hours	Rat	
Inhalation (vapor)	LC_{50}	116.9 mg/l	4 hours	Rat	
Inhalation (vapor)	LC_{50}	133.8 mg/l	4 hours	Rat	

Skin corrosion / irritation
Causes skin irritation. Data for the components of the mixture are not available.

Serious eye damage / irritation
Data for the mixture are not available. Based on the available data, the criteria for classification of the mixture are not met.

ethanol			
Route of exposure	Result	Exposure time	Species
	Irritating		Rabbit

Respiratory or skin sensitisation
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Germ cell mutagenicity
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Carcinogenicity
Data for the mixture are not available. Based on the available data, the criteria for classification of the mixture are not met.

ethanol					
Route of exposure	Parameter	Value	Result	Species	Sex
Oral			Indeterminate	Rat	

Reproductive toxicity
Data for the mixture are not available. Based on the available data, the criteria for classification of the mixture are not met.

ethanol					
Effect	Parameter	Value	Result	Species	Sex
Effects on fertility	NOAEL	>16000 ppm	No effect	Rat	
	NOAEL	5200 mg/kg/24h	Indeterminate	Rat	

Toxicity for specific target organ - single exposure
May cause drowsiness or dizziness.

ethanol							
Route of exposure	Parameter	Value	Exposure time	Specific target organ	Result	Species	Sex
Inhalation	LOAEL	2.6 mg/l	30 minutes	Nervous system	Drowsiness, Dizziness	Human	
Inhalation	LOAEL	9.4 mg/l		Lungs	Indeterminate	Human	

Toxicity for specific target organ - repeated exposure
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

Aspiration hazard
No data are available for either the mixture or the components. Based on the available data, the criteria for classification of the mixture are not met.

11.2. Information on other hazards

Endocrine disrupting properties
The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

Other information
not available

SECTION 12: Ecological information

12.1. Toxicity
Toxic to aquatic life with long lasting effects.

Acute toxicity

ethanol					
Parameter	Value	Exposure time	Species	Environment	Value determination
EC_0	3.9 g/l	200 hours	Fish		Experimentally
EC_{50}	>10000 mg/l	48 hours	Daphnia		Experimentally
IC_{50}	8800 mg/l	96 hours	Algae		Experimentally

Chronic toxicity

ethanol					
Parameter	Value	Exposure time	Species	Environment	Value determination
LC_{50}	9248 mg/l	48 hours	Invertebrates		Experimentally
NOEC	250 mg/l	120 hours	Fish (Oncorhynchus mykiss)		Experimentally
NOEC	1000 mg/l	120 hours	Fish		Experimentally

12.2. Persistence and degradability
No data are available for either the mixture or the components.

12.3. Bioaccumulative potential
No data are available for either the mixture or the components.

12.4. Mobility in soil
No data are available for either the mixture or the components.

12.5. Results of PBT and vPvB assessment
Product does not contain any substance meeting the criteria for PBT or vPvB in accordance with the Annex XIII of

Regulation (EC) No 1907/2006 (REACH) as amended.

12.6. Endocrine disrupting properties

The mixture does not contain substances with endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

12.7. Other adverse effects

Data not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Hazard of environmental contamination; dispose of the waste in accordance with the local and/or national regulations. Proceed in accordance with valid regulations on waste disposal. Any unused product and contaminated packaging should be put in labelled containers for waste collection and submitted for disposal to a person authorised for waste removal (a specialized company) that is entitled for such activity. Do not empty unused product in drainage systems. The product must not be disposed of with municipal waste. Empty containers may be used at waste incinerators to produce energy or deposited in a dump with appropriate classification. Perfectly cleaned containers can be submitted for recycling.

Waste management legislation

Directive 2008/98/EC of the European Parliament and of the Council of 19 November 2008 on waste, as amended. Decision 2000/532/EC establishing a list of wastes, as amended.

SECTION 14: Transport information

14.1. UN number or ID number

UN 1950

14.2. UN proper shipping name

AEROSOLS FLAMMABLE

14.3. Transport hazard class(es)

2 Gases

14.4. Packing group

not relevant

14.5. Environmental hazards

not relevant

14.6. Special precautions for user

Reference in the Sections 4 to 8.

14.7. Maritime transport in bulk according to IMO instruments

not relevant

Additional information

Hazard identification No.	
UN number	1950
Classification code	5F
Safety signs	2.1+hazardous for the environment



Tunnel restriction code	(D)

Air transport - ICAO/IATA

Packaging instructions passenger	203
Cargo packaging instructions	203

Marine transport - IMDG

EmS (emergency plan)	F-D, S-U
MFAG	620

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18th December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing the European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No. 793/93 and Commission Regulation (EC) No. 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, as amended. REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Commission Regulation (EU) 2020/878 of 18 June 2020 amending Annex II to Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

15.2. Chemical safety assessment

not available

SECTION 16: Other information

A list of standard risk phrases used in the safety data sheet

H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Guidelines for safe handling used in the safety data sheet

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P410+P412	Protect from sunlight. Do no expose to temperatures exceeding 50 °C.
P501	Dispose of container to in accordance with local/regional/national/international regulations.

Other important information about human health protection

The product must not be - unless specifically approved by the manufacturer/importer - used for purposes other than as per the Section 1. The user is responsible for adherence to all related health protection regulations.

Key to abbreviations and acronyms used in the safety data sheet

ADR	Agreement concerning the international carriage of dangerous goods by road
Aerosol	Aerosol
Aquatic Chronic	Hazardous to the aquatic environment (chronic)
Asp. Tox.	Aspiration hazard
BCF	Bioconcentration Factor
CAS	Chemical Abstracts Service
CLP	Regulation (EC) No 1272/2008 on classification, labelling and packaging of substance and mixtures
EC	Identification code for each substance listed in EINECS
EC_0	Concentration of a substance when it is affected 0 % of the population
EC_{50}	Concentration of a substance when it is affected 50 % of the population
EINECS	European Inventory of Existing Commercial Chemical Substances
EmS	Emergency Response Procedures for Ships Carrying Dangerous Goods
EU	European Union
EuPCS	European Product Categorisation System
Eye Irrit.	Eye irritation
Flam. Gas	Flammable gas
Flam. Liq.	Flammable liquid
IATA	International Air Transport Association

IBC	International Code For The Construction And Equipment of Ships Carrying Dangerous Chemicals
IC_{50}	Concentration causing 50% blockade
ICAO	International Civil Aviation Organization
IMDG	International Maritime Dangerous Goods
IMO	International Maritime Organization
INCI	International Nomenclature of Cosmetic Ingredients
ISO	International Organization for Standardization
IUPAC	International Union of Pure and Applied Chemistry
LC_{50}	Lethal concentration of a substance in which it can be expected death of 50% of the population
LOAEL	Lowest observed adverse effect level
log Kow	Octanol-water partition coefficient
NOAEL	No observed adverse effect level
NOEC	No observed effect concentration
OEL	Occupational Exposure Limits
PBT	Persistent, bioaccumulative and toxic
PMT	Persistent, mobile and toxic
ppm	Parts per million
Press. Gas (Comp.)	Gas under pressure: compressed gas
Press. Gas (Diss.)	Gas under pressure: dissolved gas
Press. Gas (Liq.)	Gas under pressure: liquefied gas
Press. Gas (Ref. Liq.)	Gas under pressure: refrigerated liquefied gas
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals
RID	Regulation concerning the International Carriage of Dangerous Goods by Rail
Skin Irrit.	Skin irritation
STOT SE	Specific target organ toxicity - single exposure
UN number	Four-figure identification number of the substance or article taken from the UN Model Regulations
UVCB	Substances of unknown or variable composition, complex reaction products or biological materials
VOC	Volatile organic compounds
vPvB	Very persistent and very bioaccumulative
vPvM	Very persistent and very mobile

Training guidelines

Inform the personnel about the recommended ways of use, mandatory protective equipment, first aid and prohibited ways of handling the product.

Recommended restrictions of use

not available

Information about data sources used to compile the Safety Data Sheet

REGULATION (EC) No. 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL (REACH) as amended. REGULATION (EC) No. 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL as amended. Data from the manufacturer of the substance / mixture, if available - information from registration dossiers.

More information

Classification procedure - calculation method.

Statement

The safety data sheet provides information aimed at ensuring safety and health protection at work and environmental protection. The provided information corresponds to the current status of knowledge and experience and complies with valid legal regulations. The information should not be understood as guaranteeing the suitability and usability of the product for a particular application.