

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

H2


REVISED PER ECO-11-005027

11MAR11

RK

HMR

AMP WIRE RANGE
22-20 AWG STRANDED



- 1 STAMP AMP 22-20 APPROX AS SHOWN
- 2 FOR .035 TO .100 WIRE INSULATION DIA
- 3 TONGUE MATERIAL THK .023±.002
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5 BODY: MATERIAL - COPPER ASTM B152
FINISH - OVER NICKEL PLATE (QQ-N-290) .0003 AVG EXT. THK.
- 6 SLEEVE: MATERIAL - COPPER ASTM B152
FINISH - NICKEL PL. (QQ-N-290) .00003 AVG EXT. THK.
- 7 INSULATION:
MATERIAL - TEFLON (ASTM D3295)
COLOR: GREEN

#10	.197	2500	50832-1 ON TAPE	50832-3
#8	.171	2500	50832 ON TAPE	50832-2
#10	.197	1000	LOOSE PIECE	50832-1
#8	.171	1000	LOOSE PIECE	50832
"B"	"A"	QTY	PACKAGE TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 30JAN03

CHK T MICHELUTTI 30JAN03

APVD T MICHELUTTI 30JAN03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

STE TE Connectivity

NAME
TERMINAL - TEFLON, PIDG,
STRATO-THERM, RING TONGUE,

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-50832	-

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± .02
	3 PLC ± .005
	4 PLC ± -
	ANGLES ± 1°

MATERIAL	FINISH
5 6 7	5 6 7

CUSTOMER DRAWING	SCALE 8:1	SHEET 1 OF 1	REV H2
------------------	-----------	--------------	--------