

Eaton 073203

Catalog Number: 073203

Eaton Moeller® series A-PKZ0 Shunt release (for power circuit breaker), 110 V DC, Standard voltage, DC, Screw terminals, For use with: Shunt release PKZ0(4), PKE



General specifications

Product Name	Catalog Number
Eaton Moeller® series PKZ Shunt release	073203
	EAN
	4015080732037
Product Length/Depth	Product Height
68 mm	90 mm
Product Width	Product Weight
24 mm	0.126 kg

Certifications

CE
UL Category Control No.: NLRV
CSA
CSA Class No.: 3211-05
CSA-C22.2 No. 14
CSA File No.: 165628
UL 508
UL File No.: E36332
IEC/EN 60947-4-1
UL

Features & Functions

Electric connection type

Screw connection

General

Product category

Accessories

Suitable for

Motor safety switch

Used with

Motor protective circuit-breaker

Voltage type

DC

Ambient conditions, mechanical

Mounting position

Can be fitted to left side of the motor protection switch

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

55 °C

Terminal capacities

Terminal capacity (solid/flexible with ferrule)

2 x (0.75 - 2.5) mm²

1 x (0.75 - 2.5) mm²

Terminal capacity (solid/stranded AWG)

1 x (18 - 14)

2 x (18 - 14)

Electrical rating

Operational voltage

0.7- 1.1 x Us (DC)

Short-time operation 5 s

0.7 - 1.1 x Us (AC)

Rated operational voltage (Ue) at AC - min

42 V

Rated operational voltage (Ue) at AC - max

480 V

Rated operational voltage (Ue) at DC - min

24 V

Rated operational voltage (Ue) at DC - max

250 V

Magnet system

Operational voltage

0.7- 1.1 x Us (DC)

Short-time operation 5 s

0.7 - 1.1 x Us (AC)

Contacts

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at DC - min

110 V

Rated control supply voltage (Us) at DC - max

110 V

Number of contacts (normally open contacts)

0

Power consumption

Power consumption (pick-up) at DC

3 W

Power consumption (sealing) at DC

0.5 W

Design verification

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

0 A

Static heat dissipation, non-current-dependent P_{vs}

0.5 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be

evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Brochures

[eaton-motor-protective-circuit-breaker-pke-and-communication-modul-pke-brochure-w12107613en-en-us.pdf](#)

[eaton-motor-starters-system-xstart-brochure-br03407001en-en-us.pdf](#)

Catalogs

Product Range Catalog Switching and protecting motors

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

[DA-DC-00005041.pdf](#)

[DA-DC-00004246.pdf](#)

[DA-DC-00004888.pdf](#)

[DA-DC-00004913.pdf](#)

[DA-DC-00004912.pdf](#)

[DA-DC-00004910.pdf](#)

[DA-DC-00003914.pdf](#)

[DA-DC-00004953.pdf](#)

[DA-DC-00004950.pdf](#)

[DA-DC-00004961.pdf](#)

[DA-DC-00004993.pdf](#)

[DA-DC-00004997.pdf](#)

[DA-DC-00004944.pdf](#)

[DA-DC-00005037.pdf](#)

[DA-DC-00004889.pdf](#)

[DA-DC-00004230.pdf](#)

[DA-DC-00005040.pdf](#)

[DA-DC-00004316.pdf](#)

[DA-DC-00004787.pdf](#)

[DA-DC-00004996.pdf](#)

[DA-DC-00004891.pdf](#)

[DA-DC-00004878.pdf](#)

[DA-DC-00004887.pdf](#)

[DA-DC-00004969.pdf](#)

[DA-DC-00004206.pdf](#)

[DA-DC-00004884.pdf](#)

[DA-DC-00005031.pdf](#)

[DA-DC-00004069.pdf](#)

[DA-DC-00004945.pdf](#)
[DA-DC-00004851.pdf](#)
[DA-DC-00004890.pdf](#)
[DA-DC-00004920.pdf](#)
[DA-DC-00004972.pdf](#)
[DA-DC-00004544.pdf](#)
[DA-DC-00004883.pdf](#)
[DA-DC-00004952.pdf](#)
[DA-DC-00004886.pdf](#)
[DA-DC-00004916.pdf](#)
[DA-DC-00004917.pdf](#)
[DA-DC-00004976.pdf](#)
[DA-DC-00004885.pdf](#)
[DA-DC-00004601.pdf](#)
[DA-DC-00004992.pdf](#)
[DA-DC-00004881.pdf](#)
[DA-DC-00004937.pdf](#)
[DA-DC-00004915.pdf](#)
[DA-DC-00004244.pdf](#)
[DA-DC-00004914.pdf](#)
[DA-DC-00004880.pdf](#)
[DA-DC-00004545.pdf](#)
[DA-DC-00004882.pdf](#)
[DA-DC-00004960.pdf](#)
[DA-DC-00005002.pdf](#)
[DA-DC-00004919.pdf](#)
[DA-DC-00004918.pdf](#)

Drawings

[eaton-manual-motor-starters-release-u-pkz0-accessory-dimensions.eps](#)
[eaton-manual-motor-starters-shunt-releases-u-pkz0-accessory-3d-drawing.eps](#)
[eaton-manual-motor-starters-release-u-pkz0-accessory-3d-drawing.eps](#)

eCAD model

[ETN.073203.edz](#)

Installation instructions

[IL03402034Z](#)

Installation videos

[Video Motor Protective Circuit Breaker PKE](#)
[WIN-WIN with push-in technology](#)

[mCAD model](#)

[DA-CD-a_pkz](#)

[DA-CS-a_pkz](#)

Sales notes

[eaton-pke-modbus-rtu-modul-flyer-fl034008en-en-us.pdf](#)

Wiring diagrams

[eaton-manual-motor-starters-release-a-pkz0-shunt-release-wiring-diagram.eps](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)