

LC CONN. MARK		LC CONN. MARK
A	↔	B
B	↔	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm OR 1300 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2RETURN LOSS ≥ 20 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
- 3TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4CABLE INFORMATION:


— CORE DIAMETER:50/125 μm

— OUTER JACKET DIAMETER:1.8x3.6 mm

— OUTER JACKET COLOUR:ORANGE

— OUTER JACKET MATERIAL:LSZH
- 5BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061310-Y	XY.0

2	BLANK LABEL				3			
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE				2			
L	FOCAB 1.8MZ 50/125, ORANGE, LSZH				1			
Qty	Description				Item			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	Tyco Electronics Tyco Electronics Corporation 's-Hertogenbosch, Nederland NAME FIBER OPTIC LEAD 1.8MZ LC/DPX - LC/DPX MULTI MODE 50/125 SIZE CAGE CODE DRAWING NO RESTRICTED TO					
DIMENSIONS:		CHK A. HENGELMOLEN 16OCT2009						
mm		APVD A. HENGELMOLEN 16OCT2009						
		PRODUCT SPEC						
		APPLICATION SPEC						
MATERIAL		WEIGHT	A2	00779	C=2061310	—		
FINISH		CUSTOMER DRAWING	SCALE	NTS	SHEET	1 of 1	REV	A