



# **Product:** <u>RKT 4-3-06</u> □


M12 Standard Sensor/Actuator Single-Ended Cordset: Female, straight, 4-pin, A-coded, translucent body, 230 V AC/DC, 4 A; PVC orange cable, 3-wires, 0.34 mm<sup>2</sup>

## **Product Description**


M12 Standard Sensor/Actuator Single-Ended Cordset: Female, straight, 4-pin, A-coded, translucent body, 230 V AC/DC, 4 A; PVC orange cable, 3-wires, 0.34 mm²

#### **Technical Drawing**





# Female



## **Technical Specifications**

#### Face View



#### **Technical Data**

Product Family:	Sensor / Actuator Connectors
Product Sub Family:	M12 Standard
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Female
Connector Design:	Straight
Number of Pins:	4
Coding:	A
Shielding:	Unshielded
Attachment Type:	Coupling Nut
Rated Voltage:	250 V
Rated Voltage (UL):	250 V AC
Rated Impulse Voltage:	2.5 kV
Operating Voltage:	230 V AC/DC
Rated Current*:	4 A
Rated Current (UL)*:	4 A

Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Operating Temperature (UL):	max. + 50 °C
Protection Degree / IP Rating**:	IP65, IP67
Design Standard:	IEC 61076-2-101
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	II acc. to DIN EN 60664-1 (VDE 0110-1)

## **Materials**

Contact Base Material:	CuSn
Contact Plating:	Cu/Au
Contact Bearer Material:	TPU
Contact Bearer Color:	Orange
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	TPU
Molded Body Color:	Translucent
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Nickel-plated
O-Ring Material:	FKM, green

#### **Additional Technical Data**

Fastening Torque (Attachment): M 12x1: (50-60) Ncm, hand-tight	Fastening Torque (Attachment):
--	--------------------------------

## **Cable Data**

Cable Number:	006			
Conductor Size:	0.34 mm²			
Number of Wires:	3			
Minimal Bending Radius (Fixed Inst):	>5 x D			
Minimal Bending Radius (Flexible Inst):	> 10 x D			
Cycles (Bending):	>1 M			
Conductor material:	Cu			
Cable Jacket Material:	PVC			
Cable Jacket Color:	orange			
Cable Diameter D:	ø 5.0 ± 0.2 mm			
Wire Insulation Material:	PVC			
Insulated Wire Diameter:	ø 1.50 mm			
Ambient Temperature (Fixed Installation):	- 40 °C - + 90 °C (UL: + 80 °C)			
Ambient Temperature (Flex Installation):	+ 5 °C - + 90 °C (UL: +80 °C)			
Ambient Temperature (Drag Chain Inst):	+ 5 °C - + 60 °C			
UL Cable Type:	AWM: 2464			
Flammability Class (Cable Jacket):	DIN EN 60332-1-2, VDE 0482-332-1-2, IEC 60332-1-2, UL VW-1			
Cable Characteristics:	Free of lacquer wetting disturbing substances; Exclusion of silicone			

# **Approvals**

ı	JL-File:	E315587
ı	JL:	UL 2238; cURus

# Safety & Environmental Compliance

RoHS Compliant:	yes	l
-----------------	-----	---

## Resistances

Oil Resistance:	Good chemical and oil resistance	

## Notes

Note Derating:	Notice derating

Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector	
Note:	Do not connect or disconnect under load.	

#### Variants

Item #	Item Description	Cable Length	Rated Current	Contact Bearer Color
1245	RKT 4-3-06/20 M	20 m	4 A	Orange
1246	RKT 4-3-06/30 M	30 m	4 A	Orange
11362	RKT 4-3-06/10 M	10 m	4 A	Orange
11363	RKT 4-3-06/2 M	2 m	4 A	Orange
11364	RKT 4-3-06/5 M	5 m	4 A	Orange
11429	RKT 4-3-06/3 M	3 m	4 A	Orange
18917	RKT 4-3-06/3,3 M	3.3 m	4 A	Orange

© 2022 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.