



Connectors > Automotive Connectors > Automotive Housings > AMPSEAL 16 Housings



Number of Positions: 6

Connector & Housing Type: **Housing for Male Terminals**

Mating Pin Diameter: 1.5 mm [.062 in]

Connector System: **Wire-to-Wire**

Centerline (Pitch): 4.5 mm [.177 in]

[All AMPSEAL 16 Housings \(224\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------



Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	B

Contact Features

Contact Size	Size 16
Contact Type	Pin
Mating Pin Diameter	1.5 mm[.062 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF15
Centerline (Pitch)	4.5 mm[.177 in]

Dimensions

Row-to-Row Spacing	5.3 mm[.209 in]
Compatible Insulation Diameter Range	1.3 – 2.3 mm[.051 – .131 in]
Product Width	47.55 mm[1.87 in]
Product Length	24.6 mm[.968 in]
Connector Height	26.8 mm[1.05 in]
Wire Size	20 – 14 AWG

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

IP Rating	IP67
-----------	------



UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	50
Packaging Method	Bag

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27519360985) Decamethylcyclopentasiloxane (D5) (.5% in 27519360985) Octamethylcyclotetrasiloxane (D4) (.5% in 27519360985) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CAT-AM7801-P729
AMPSEAL 16 Connectors Sealing Plugs



TE Part # CAT-AM7801-T273
AMPSEAL 16 CONTACTS



TE Part # CAT-AM7801-M8649
AMPSEAL 16 Connectors Mounting Clips



TE Part # CAT-AM7801-T618
Removal Tools — AMPSEAL 16



TE Part # 776531-2
AS16, PLUG ASSY, ST, 06P, E SEAL, CODE B




TE Part # CAT-AM7801-B128
AMPSEAL 16 Connectors Backshell

Also in the Series | AMPSEAL 16



Automotive Connector Locks & Position Assurance(6)



Automotive Housings(239)



Connector Backshells(84)




Connector Seals & Cavity Plugs(10)



Data Connectivity Headers(2)



Data Connectivity Housings(3)



Other Automotive Connector Accessories(8)



Rectangular Backshells & Clamps(74)

Customers Also Bought



TE Part #HDC16-9
DUST CAP ASM



TE Part #0462-201-16141
SOC, SOLID, SIZE 16, 16-20AWG, NI



TE Part #CAT-J41-DDRC
DEUTSCH DT Receptacle Connectors



TE Part #DT06-08SB-P012
PLG, 8P, BLK, N, SEAL RET, B



TE Part #776430-1
AS16,CAP ASSY,ST,03P,N SEAL,CODE A



TE Part #W8S-P012
WEDGE LOCK, 8P, PLG, GRN, SL RET, DT



TE Part #HD10-9-96P-B009
REC, 9P, GRY, N, NO KEY, FLANGE, 16



TE Part #DRC18-40SA-P013
PLG, 40P, BLK, N, SEAL BOND, A

Documents

Product Drawings

CAP ASSY,6P,BRACKET REVERSE TYPE,ATAC CO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1717975-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1717975-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1717975-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

1717975-2

6 Position Housing, Housing for Male Terminals, Wire-to-Wire, 4.5 mm [.177 in]
Centerline, Sealable, Black, Wire & Cable, Power, AMPSEAL 16

