# 1FHP,64,30A/P,S,N,S10,12,13,15 - ACTIVE

TE Part # 120527-1

TE Internal #: 120527-1

View on TE.com >



Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles











PCB Connector Assembly Type: PCB Mount Header

PCB Mount Orientation: Vertical
Connector System: Board-to-Board

Number of Positions: 64

Centerline (Pitch): 1 mm [ .039 in ]

#### **Features**

#### **Product Type Features**

Series	1mm FH
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### **Configuration Features**

Number of Rows	2
Number of Columns	32
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	64
Board-to-Board Configuration	Mezzanine

### **Electrical Characteristics**

Insulation Resistance	2 ΜΩ
Operating Voltage	250 VAC

### Signal Characteristics



Differential Signaling	Yes
Contact Features	
Contact Layout	Inline
Contact Underplating Material Thickness	1.27 μm[50 μin]
PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Mating Post Length	2 mm
PCB Contact Termination Area Plating Material Finish	Matte
Contact Configuration	Single Beam
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 μm[29.9212 μin]
Contact Type	Pin
Contact Current Rating (Max)	1 A
Termination Features	
Termination Method to Printed Circuit Board	Surface Mount
Mechanical Attachment	
PCB Mount Alignment Type	Locating Posts
Mating Retention	Without
PCB Mount Retention Type	None
Mating Alignment	Without
Mating Alignment Type	None
PCB Mount Retention	Without
PCB Mount Alignment	With
Housing Features	
Mating Entry Location	Тор
Centerline (Pitch)	1 mm[.039 in]
Housing Color	Black
Housing Material	Matte
Dimensions	
Connector Length	34.22 mm[1.347 in]
Connector Height	8.35 mm[.328 in]



Connector Width	3.81 mm[150 in]
Stack Height	9 mm, 11 mm, 14 mm[.551 in]
Usage Conditions	
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]
Operation/Application	
Assembly Process Feature	None
Circuit Application	Signal
Industry Standards	
Industry Standard	IEEE 1386
UL Flammability Rating	UL 94V-0
Agency/Standard	CSA, UL
CSA Certified	Yes
CSA File Number	LR7189
UL File Number	E28476
UL Rating	Listed
Packaging Features	
Packaging Quantity	400

Packaging Quantity	400
Packaging Method	Tape & Reel

## **Product Compliance**

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

# **Compatible Parts**



# **Customers Also Bought**





TE Part #1410968-3
MULTIGIG RT2 7RW RTM
DC DF CT



TE Part #1-1469492-3 MULTIGIG RT 9MM GUIDE /ESD 90 DEG



TE Part #1-1469492-2 MULTIGIG RT 9MM GUIDE /ESD 45 DEG



2ACP+1LP+32S+3HDP+1LP+1P/ESD 270 DEG



MULTIGIG RT 9MM GUIDE





TE Part #120521-1 1FHR,64,30A/P,S,N,S08, 09,10





TE Part #5120527-1 1FHP,64,30A/S,S,N,S10, 12,13,15



### **Documents**

### **Product Drawings**

1FHP,64,30A/P,S,N,S10,12,13,15

English

#### **CAD Files**

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_120527-1\_F1.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_120527-1\_F1.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_120527-1\_F1.3d\_stp.zip

English

### **Product Specifications**

**Application Specification** 

English

### Product Environmental Compliance

TE Material Declaration

English