

## Features

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.

## RS PRO Oilite® Flanged Bearing

RS Stock No.: 0529026




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

RS PRO is offering range of Oilite® plain bearings - self-lubricating bearings that are made from metal alloys with pores that channel lubricants between the bearing itself and the shaft.

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Lubricant : Shell Tellus S2 MX68
- Temperature range of -15°C to +75°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.
- All dimensions and tolerances of our metric ranges conform to ISO 2795:1991
- Wide range of metric and imperial sizes
- Wide range of different types: Plain, Flanged

\* Below dimensions in mm



## Specifications

### Details

Inner Diameter	14	Outer Diameter	20	Length	20
Tolerance Range	UK Standard	Flange Thickness	3	Flange Diameter	26

### Material Specification

Structure	Oil impregnated sintered bronze*		
Max PV (N/mm <sup>2</sup> x m/s)	1.8	Max Static load (N/mm <sup>2</sup> )	50
Max Dynamic load (N/mm <sup>2</sup> )	14	Max Sliding speed (m/s)	5
Operating temperature (°C)	-60 to 200* *dependant on lubrication	Density (g/cm <sup>3</sup> )	6.6
Radial crushing strength (K Min M/mm <sup>2</sup> )	160		

### Tolerances & Fittings (Metric)

	Min	Max	Tolerance
Inside Diameter	14.006	14.024	G7
Outside Diameter	20.035	20.056	s7
Overall Length	19.835	20.165	js13
Flange Thickness Tolerance	2.930	3.070	js13
Flange Diameter Tolerance	25.835	26.165	js13
Recommended Housing Size	20.000	20.021	H7
Shaft Diameter	13.966	13.984	f7
Fitting Pin Size	14.007	14.015	m5
Concentricity Max	0.052	0.052	IT9
Inside Diameter When Fitted	14.000	14.018	H7