

QS 9 FH BLUE

Torque screwdriver Type Quickset

0.24 - 9 Nm

Code **7718210** ETIM **EC002132**

EAN **4002805757093** UNSPSC **27-11-27-20**

Country of origin **Germany** eCl@ss **21-04-02-22**

Customs tariff number
82041100



Article description

- Use:
- Controlled screw tightening in the range of 4 - 9 Nm
- High-speed, controlled tightening enables serial production
- Electrical and electronic hardware industry, instrument-making industry and industrial manufacturing or in quality control
- Features:
- Adjustable Torque Wrench - with Single Scale
- With 1/4" female hexagon drive for use with 1/4" hexagon bits as per DIN 3126 - C 6.3
- Working accuracy: +/- 6 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Precision radial ball clutch and cam design for controlled bi-directional tightening
- Precision mechanism slips very noticeably when the pre-set value is achieved
- Automatic resetting to the starting position
- 3 models ranging from 0.2 Nm to 9 Nm, with additional models available in lbf-in and ozf-in
- Micrometre scale graduation: 1 cNm resp. 0,1 Nm
- Lightweight construction by virtue of anodised aluminium handgrips
- Scope of delivery:
- Torque screwdriver QUICKSET 9 FH
- Including additional cross handle for easier operation
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

Contents [Qty of pieces]	1	Torque range [min./max.] [N·m]	4 Nm - 9 Nm
Net weight [kg]	0,335 kg	Epo-/Esd-Model	no
Total length [mm]	184 mm	Trigger mechanism	Friction clutch
Total height [mm]	35 mm	Precision +/-	+/- 6 %
Drive connector hexagon female [inch]	1/4"	Direction of tightening	Left and right
Drive connector hexagon female (metric)	6,3	Fixed setting	yes
Drive type/drive	Bitholder	Test certificate	DIN EN ISO 6789-2:2017
Torque (min.) [N·m]	4 Nm	Torque range [min./max.] [cN·m]	-
Torque (max.) [N·m]	9 Nm	T-handle available	no