




MOSC41-20-SS

Ruland MOSC41-20-SS, 20mm Oldham Coupling Hub, 303 Stainless Steel, Set Screw Style With Keyway, 41.3mm OD, 18.0mm Length



Description

Ruland MOSC41-20-SS is a set screw oldham coupling hub with a 20mm bore, 6mm keyway, 41.3mm OD, and 18.0mm length. It is a component of a three-piece design consisting of two stainless steel hubs press fit onto a center disk. This three-piece design allows for a highly customizable coupling that easily combines clamp or set screw hubs with inch, metric, keyed, and keyless bores. Disks are available in three materials allowing the user to tailor coupling performance to their application. MOSC41-20-SS can accommodate all forms of misalignment and is especially useful in applications with high parallel misalignment (up to 10% of the OD). It operates with low bearing loads protecting sensitive system components such as bearings and has a balanced design for reduced vibration at speeds up to 6,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MOSC41-20-SS is machined from bar stock that is sourced exclusively from North American mills and is RoHS3 and REACH compliant. It is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	20 mm	Keyway (K)	6 mm
Outer Diameter (OD)	1.625 in (41.3 mm)	B1 Max Shaft Penetration	18.0 mm
Bore Tolerance	+0.03 mm / -0.00 mm	Hub Width (LH)	18.00 mm
Length (L)	2.000 in (50.8 mm)	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
Forged Set Screw	M5	Number of Screws	2 ea 90° apart
Screw Material	18-8 300 Series Stainless Steel	Screw Finish	Bright
Seating Torque	3.2 Nm	Hex Wrench Size	2.5 mm
Torque Specifications	Torque ratings vary with insert selection	Angular Misalignment	0.5°
Parallel Misalignment	0.010 in (0.25 mm)	Max Parallel Misalignment	0.163 in (4.13 mm)
Axial Motion	0.006 in (0.15 mm)	Moment of Inertia	4.1688 x 10 ⁻⁵ kg-m ²
Maximum Speed	4,500 RPM	Recommended Inserts	OD26/41-AT , OD26/41-NL , OD26/41-PEK
Full Bearing Support Required?	Yes	Zero-Backlash?	Yes
Balanced Design	Yes	Mechanical Fuse?	Yes
UPC	634529239216	Country of Origin	USA
Material Specification	Type 303 Austenitic, Non-Magnetic Bar	Finish	Bright
Finish Specification	Bright, No Plating	Manufacturer	Ruland Manufacturing
Temperature	Acetal Disk -10°F to 150°F (-23°C to 65°) Nylon Disk -10°F to 130°F (-23°C to 54°C) PEEK Disk -10°F to 300°F (-23°C to 148°C)	Weight (lbs)	0.347000
Tariff Code	8483.60.8000	UNSPC	31163015
Note 1	"Performance ratings are for guidance only. The user must determine suitability for a particular application."		

Note 2	"Torque ratings for the couplings are based on the physical limitations/failure point of the torque disks. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the disks. Please consult technical support for more assistance."
---------------	--

Prop 65

WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

Installation Instructions

1. Align the bores of the MOSC41-20-SS oldham coupling hubs on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misalignment: 0.5° Parallel Misalignment: 0.010 in (0.25 mm), Axial Motion: 0.006 in (0.15 mm)*)
2. Rotate the hubs on the shaft so the drive tenons are located 90° from each other.
3. Place a torque disk so one groove fits over the drive tenons of a hub and center the disk by hand.
4. Insert a shim with the thickness of the coupling's axial motion rating into the groove of the torque disk.
5. Slide the tenons of the second hub into the mating groove in the disk until it touches the shim stock.
6. Fully tighten the M5 screw(s) on each hub to the recommended seating torque of 3.2 Nm using a 2.5 mm hex torque wrench.
7. Remove the shim stock to leave a small gap between the top of the drive tenons and the torque disk to allow for axial movement.