

Description

CONDUCTIVE CASTOR WITH TOP PLATE, GREY POLYURETHANE RUBBER 80MM

Fixed
EF4BA080-271B-PF




Swivel
EP4BA080-272B-PF



Swivel and brake
EP4BD080-272B-PF



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	80 mm		
Overall Height H	108 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	38 mm	38 mm
Width of Tread	32 mm±0,5		
Hardness of tread	shore A ± 90		
Load capacity	120 Kg		
Weight	0,56 kg	0,64 kg	0,75 kg
Temperature	- 20 / + 70 °C		



Castor Assembly :

Pressed steel, zinc-plated components. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of Grey electroconductive Polyamide 6.
Tread : Dark grey Polyurethane made from electroconductive materials.
Hub : Sealed ball bearing. Polyamide Threadguards.

Features :

Low starting effort,
Bonded Rubber, non marking.
Good resistance to abrasion and chemical aggression.
Protects sensitive goods and users from electric shocks (electrostatic discharges).
Conductive casters compliant with ISO 22877.
Electrical resistance < 100000 ohms.
For use on trolleys or sensitive devices in laboratories, medical units, hospitals, electrical and electronic factories, explosion hazard areas....