




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Multiple Contact Types	Without
Contact Layout	Matrix
Contact Type	Socket
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	4.2 mm[.165 in]

Dimensions

Row-to-Row Spacing	4.14 mm[.163 in]
Connector Width	22.4 mm
Connector Height	16 mm
Connector Length	23.7 mm

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170360-1
UNIV M-N-L PIN 22-18 AWG



TE Part # 171637-1
MINI U-M-N-L SOCKET CONTACT



TE Part # 170365-1
MINI UNIVERSAL M-N-L SOCKET LP






TE Part # 170362-1
UNIV M-N-L SOC. 22-18 AWG



 TE Part # 170366-1 MINI UNIVERSAL M-N-L SOCKET LP	 TE Part # 770988-1 MINI UMNL SOK 22-18AWG SN LP	 TE Part # 171636-1 MINI U-M-N-L PIN CONTACT	 TE Part # 1-770901-0 MINI UMNL PIN 26-22 AWG AU LF
 TE Part # 1-770903-0 MINI UMNL PIN 22-18 AWG AU	 TE Part # 170360-4 MINI UNIVERSAL M-N-L PIN	 TE Part # 170365-4 MINI UNIVERSAL M-N-L SOCKET LP	 TE Part # 170359-1 UNIV M-N-L PIN 26-22 AWG
 TE Part # 1-794058-0 MINI UMNL SOK L/P LF	 TE Part # 1-770904-0 MINI UMNL SOK 22-18 AWG AU	 TE Part # 1-770986-0 MINI UMNL SOK 26-22AWG AU LP	 TE Part # 1-770987-0 MINI UMNL PIN 22-18 AWG AU LP
 TE Part # 770834-4 MINI UMNL SOCKET PHBR	 TE Part # 770902-3 MINI UMNL SOK 26-22 AWG AU	 TE Part # 770902-6 MINI UMNL SOK 26-22 AWG AU	 TE Part # 1-794059-0 MINI UMNL PIN L/P LF

Also in the Series | Mini-Universal MATE-N-LOK


 Connector Caps & Covers(2)	 Connector Contacts(89)	 Connector Hardware(4)	 Power Contacts(89)
---	--	--	---



Rectangular Connector Housings(104)



Rectangular Power Connectors(196)



Standard Rectangular Connectors(104)


Customers Also Bought



TE Part #2-34853-1
TERM,PG, R, 12-10, #8, T&R



TE Part #770827-1
04P CMNL PLUG HSG 94-VO



TE Part #2-794954-4
24P RCPT VAL-U-LOK V2



TE Part #1-2271656-1
MINI IO VERTICAL SMT PLUS REC CONN KIT




TE Part #5670416008
TSAS-NR501-X-10MM



TE Part #3-640433-2
02P MTA156 CONN ASSY 22AWG RED



TE Part #1658537-1
SOCKET CONT DUPL PLT STRIP HD-



TE Part #2-87195-4
MOD IV RECP PLTE 15 DPLX



TE Part #172334-1
MINI UMNL CAP HOUSING 15P



TE Part #350669-1
UMNL GRND PIN 20-14 PTPBR L/P

Documents

Product Drawings

MINI UMNL PLUG HOUSING 15P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172342-1_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_172342-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_172342-1_F.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_172342-1_A1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_172342-1_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_172342-1_A1.3d_stp.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English