



Part Number : [510150200](#)
Product Description : 2.00mm Pitch, Board-In
Crimp Housing, Vertical, 2 Circuits, Natural
Series Number : 51015
Status : Active
Product Category : Connector Housings



Documents & Resources


Drawings
[510150200_sd.pdf](#)

3D Models and Design Files
[510150200_stp.zip](#)

Specifications
[510159200-SPK-200.pdf](#)
[510151002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	51015
Description	2.00mm Pitch, Board-In Crimp Housing, Vertical, 2 Circuits, Natural
Application	Signal, Wire-to-Board
Product Name	Board-in
UPC	800753749245

Physical

Circuits (maximum)	2
Color - Resin	Natural
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.048/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Use with Part(s)

Description	Part Number
2.00mm Pitch Board-in Vertical Male Crimp Terminals	<u>50034</u>

This document was generated on Apr 23, 2025