


Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KETF10MPN

COUPLING HALF: Coupler

FUNCTION: Self-Venting

CONNECTION TYPE: Hose Barb

BODY MATERIAL: Brass

CONNECTION SIZE: 10 MM

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:

- General Industrial
- Industrial manufacturing equipment

Features/Benefits:

- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

INDUSTRY	Transportation
COMPATIBLE FITTING	Series 25 Plug
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
INDUSTRY	General Industrial
LENGTH	71 mm
VALVE INCLUDED	Yes
APPLICATION	Energy Management
SLEEVE MATERIAL	Brass
VALVE TYPE	Standard Valve
SEAL MATERIAL	NBR
APPLICATION	Electronics
CONNECTION TYPE	Hose Barb
REGION OF ORIGIN	Germany
HEX SIZE	22 mm
FUNCTION	Self-Venting
OPERATION TYPE	Sleeve
PRODUCT TYPE	Pneumatic Quick Couplings
BODY MATERIAL	Brass
APPLICATION	Air & Gas Compressor
TECHNOLOGY	Pneumatics
PRODUCT STYLE	Quick-Connect
DIVISION	Low Pressure Connectors Europe Division
OUTSIDE DIAMETER	31 mm
PLATING TYPE	Nickel-Plated
APPLICATION	Mobile & Defence
COUPLING HALF	Coupler

QUANTITY PER BOX	5
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Trucks & Trailers
MINIMUM OPERATING TEMPERATURE	-20 °C
CONNECTION SIZE	10 mm
WEIGHT	0.095 kg
MINIMUM OPERATING TEMPERATURE	-4 °F
BRAND	Rectus
MAXIMUM OPERATING PRESSURE	174 psi
INDUSTRY	Electronics
MAXIMUM OPERATING TEMPERATURE	140 °F
INTERCHANGE TYPE	European Profile
PRODUCT SERIES	Series 26
MAXIMUM OPERATING PRESSURE	12 bar
FLOW RATE	830 L/min (air)
MAXIMUM OPERATING TEMPERATURE	60 °C
BRAND	Parker
DIAMETER	7.4 mm (nominal)