

Eaton 266713

Catalog Number: 266713

Eaton Moeller series NZM - Molded Case Circuit Breaker. Socket base, 3p, 1600A



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM plug-in unit	266713
EAN	Product Length/Depth
4015082667139	509 mm
Product Height	Product Width
295 mm	250 mm
Product Weight	Compliances
17.28 kg	IEC
	RoHS conform
Certifications	
IEC/EN 60947	

Product specifications

Type

Accessory Extension base for basic unit

Features

Version as built-in device

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM4](#)

Drawings

[eaton-circuit-breaker-withdrawable-unit-nzm-mccb-dimensions.eps](#)

[eaton-circuit-breaker-padlock-nzm-rotary-handle-dimensions.eps](#)

[eaton-circuit-breaker-socket-nzm-socket-base-3d-drawing.eps](#)

eCAD model

[ETN.266713.edz](#)

Installation instructions

[eaton-circuit-breaker-voltage-release-nzm4-il012143zu.pdf](#)

[eaton-circuit-breaker-withdrawable-unit-nzm3-4-il01219018z.pdf](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CS-nzm4_xavs](#)

[DA-CD-nzm4_xavs](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Frame

NZM4

Mounting Method

Withdrawable

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

76.8 W

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Nominal current

1488 A

Protection against direct contact

Finger and back-of-hand proof to VDE 0106 part 100

Terminal equipment included

Screw connection

Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

Degree of protection

IP2X (in the area of the plug-in area)

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Mounting position

Vertical

Number of poles

Three-pole

Shock resistance

15 g (half-sinusoidal shock 11 ms)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia