

WB 34-632P

WHEAT LACE UP ANKLE BOOT



by Honeywell

STYLE SPECIFICATIONS

DESCRIPTION:

Premium nubuck water resistant leather lace up ankle boot.

Colour: Wheat

Sizes: 4 - 13, 6½ - 10½

Standards:

AS/NZS 2210.3:2019

EN ISO 20345:2011 ASTM F2413-18

Application: Agriculture / Building & Construction / Manufacturing / Food Processing / Hospitality / Commercial Kitchens / Mining & Quarrying / Transport & Logistics / Storage & Warehouse

**REPLACEMENT
LACE CODE: L-G0125**

EXTRA FEATURES:



ANTISTATIC



SOLE
PENETRATION
SOLUTION



FEATURES:

- Water resistant nubuck leather.
- Padded collar and tongue.
- Full lining and footbed treated with eco-friendly Odorban™ Control Technology to absorb odour for optimum freshness & hygiene.
- COMFORTcushion® Impact Absorption System with PORON® protects the heel and ball of the foot.
- Comfort footbed with perforated air channels to enhance natural airflow.
- NATUREform® steel toe cap with a wide profile for greater comfort.
- GRIPthane® dual density polyurethane sole with lightweight shock absorbing PU midsole and hard wearing outsole for superior durability; resistant to 130°C surface contact.
- Excellent slip resistant sole; SRC slip resistant classification.
- Sole resistant to mineral & organic oils & acids. Cut, split and crack resistant.
- Minimises the build up of electrostatic charges and provides protection against the risk of spark ignition for such hazards as flammable materials and gases
- Offers the reduced risk of sharp objects penetrating the sole and entering the foot.

COMFORT TECHNOLOGY



COMFORTcushion
Impact
Absorption



NATUREform
wide profile Type
1 safety toe cap



Water Resistant
Leather



Steel Safety
Toe Cap



Antimicrobial
Technology

SOLING TECHNOLOGY



130°C
Heat Resistant
sole (266° F)



Abrasion
Resistant sole



Cut Resistant
sole



Slip Resistant
sole



Sole resistant to
mineral oils
and acids



Sole resistant to
organic oils
and fats



HYDROstop
3 year guarantee
against hydrolysis



Antistatic



Sole Penetration
Solution

Oliver Safety Footwear

by Honeywell

Kingshoe Manufacturing Pte Ltd
17 Changi Business Park Central 1
Singapore 486041

hsp.asean@Honeywell.com

Singapore : +65 6714 6800
Malaysia : +603 2777 3948 / 3950
Indonesia : +62 21 2964 0328
Philippines : +632 730 7300
Thailand : +66 2 693 3099
Vietnam : +8428 5411 2260

MORE INFO:



oliver.com.au

Honeywell