

SG11811



Description

- Top-quality miniature circuit breakers 1P+N with a width of 1 module unit requiring little space for installation
- Contact position indicator red - green
- Guide for secure terminal connection
- Comprehensive range of accessories for subsequent installation
- Rated currents up to 40 A
- Tripping characteristics B, C
- Rated breaking capacity 6 kA according to IEC/EN 60898

SG11811



Rated current I_n (A)	Type Designation	Article No.	Units per package
----------------------------	---------------------	-------------	----------------------

6 kA, Characteristic B

1+N-pole			
6	PLG6-B6/1N	264672	12/120
10	PLG6-B10/1N	264673	12/120
13	PLG6-B13/1N	264674	12/120
16	PLG6-B16/1N	264675	12/120
20	PLG6-B20/1N	264676	12/120
25	PLG6-B25/1N	264677	12/120
32	PLG6-B32/1N	264678	12/120
40	PLG6-B40/1N	264679	12/120

SG11811



6 kA, Characteristic C

1+N-pole			
2	PLG6-C2/1N	264690	12/120
4	PLG6-C4/1N	264691	12/120
6	PLG6-C6/1N	264692	12/120
10	PLG6-C10/1N	264693	12/120
13	PLG6-C13/1N	264694	12/120
16	PLG6-C16/1N	264695	12/120
20	PLG6-C20/1N	264696	12/120
25	PLG6-C25/1N	264697	12/120
32	PLG6-C32/1N	264698	12/120
40	PLG6-C40/1N	264699	12/120

Specifications | Miniature Circuit Breakers PLG

Description

- High selectivity between MCB and back-up fuse due to low let-through energy
- Profile compatible with other devices of the Xpole series, bridging with the PFGM RCD circuit breaker is possible
- Colour of the switching toggle according to the performance rating of the circuit breaker
- Meets the requirements of insulation co-ordination, distance between contacts > 4 mm, for secure isolation
- Rated breaking capacity $I_{cn1} = 3 \text{ kA}$
- N-Links

Technical Data


PLG	
Electrical	
Design according to	IEC/EN 60898
Current test marks as printed onto the device	
Rated voltage	U_n
AC	230 V
DC	48 V
Rated frequency	50/60 Hz
Rated breaking capacity	
PLG6	6 kA
PLG4	4.5 kA
Characteristic	B, C
Back-up fuse	
>6 kA	max. 100 A gL/gG
>4.5 kA	max. 80 A gL/gG
Selectivity class	3
Endurance electrical components	$\geq 8,000$ operating cycles
Mechanical	
Frame size	45 mm
Device height	80 mm
Device width	17.5 mm per pole (1MU for 1p+N)
Mounting	quick fastening with 2 lock-in positions on DIN rail EN50022
Degree of protection	IP20
Upper and lower terminals	open mouthed/lift terminals
Terminal protection	finger and hand touch safe, DGVV VS3, EN 50274
Terminal capacity	1x (1.5 - 35) mm ² single wire 2x (1.5 - 16) mm ² multi wire
Terminal cross-section	1-16 mm ²

Connection diagram

1-pole + N




Dimensions (mm)




Load rating – Effect of ambient temperature PLG6


Load Capacity of Series Connected PLG6




Effect of ambient temperature ($I_n = 2-13$ A)



Effect of ambient temperature ($I_n = 16-25$ A)




Effect of ambient temperature ($I_n = 32, 40$ A)




mitted permanent load at ambient temperature T (°C) with n devices $I_{DL} = I_n K_T (T) K_N (N)$

Let-through energy PLG6

Let-through energy PLG6, Characteristic B, 1+N-pole




Let-through energy PLG6, Characteristic C, 1+N-pole




Load rating – Effect of ambient temperature PLG4


Load Capacity of Series Connected PLG4




Effect of ambient temperature ($I_n = 2-13\text{ A}$)



Effect of ambient temperature ($I_n = 16-25\text{ A}$)




Effect of ambient temperature ($I_n = 32, 40\text{ A}$)



mitted permanent load at ambient temperature T (°C) with n devices $I_{DL} = I_n K_T(T) K_N(N)$

Let-through energy PLG4

Let-through energy PLG4, Characteristic B, 1+N-pole



Let-through energy PLG4, Characteristic C, 1+N-pole

