



Part Number : [1042679617](#)

Product Description : 0.50mm Pitch Easy-On FFC/
FPC Wide Slim Connector, Right-Angle, ZIF, Surface
Mount, Double Bottom Contact Style, 1.50mm Height,
96 Circuits

Series Number : 104267

Status : Active

Product Category : FFC / FPC Connectors



Documents & Resources

Drawings

[1042679617_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[1042679617.dxf](#)


Specifications

[SPK-104267-001-001.pdf](#)

[PS-104267-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	104267
Description	0.50mm Pitch Easy-On FFC/FPC Wide Slim Connector, Right-Angle, ZIF, Surface Mount, Double Bottom Contact Style, 1.50mm Height, 96 Circuits
Comments	Black actuator
Product Name	Easy-On
UPC	889056496858

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	96
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	1.50mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	0.645/g
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	FFC/FPC