



Fuse-link, low voltage, 32 A, AC 660 V, DC 460 V, 80 kA, BS88/A2, 22 x 86 mm, gM, BS, motor-rated



Part no. **32M50A 660V AC / 460V gM DC FUSE**
 Catalog No. **TIA32M50**

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	32
Motor current rating	I	A	32M50
Rated voltage			AC 660 V DC 460 V
Construction size			BS88/A2
Size			22 x 86 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder CM32F and RS32

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	32
Rated voltage		V	660
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No