

# Eaton 240869

Catalog Number: 240869

Eaton Moeller series xEffect - FAZ-T MCB. FAZ-T, 2-pole, tripping characteristic: D, rated current In: 10 A



## General specifications

| Product Name                             | Catalog Number |
|------------------------------------------|----------------|
| Eaton Moeller series xEffect - FAZ-T MCB | 240869         |
|                                          | EAN            |
|                                          | 4015082408695  |
| Product Length/Depth                     | Product Height |
| 80 mm                                    | 75.5 mm        |
| Product Width                            | Product Weight |
| 36 mm                                    | 0.22 kg        |
| Compliances                              | Certifications |
| RoHS conform                             | IEC/EN 60947-2 |
|                                          | EN45545-2      |
|                                          | IEC 61373      |

## Product specifications

### Used with

FAZ-T

Miniature circuit breaker

### Type

FAZ-T

Miniature circuit breaker

### Special features

Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity

### Application

Switchgear for industrial and advanced commercial applications  
xEffect - Switchgear for industrial and advanced commercial applications

### Amperage Rating

10 A

### Features

Additional equipment possible

#### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

#### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

## Resources

### Brochures

[eaton-pdd-railrolling-stock-brochure-br011002en-en-us.pdf](#)

### Catalogs

[eaton-xeffect-faz-t-mcb-catalog-ca003035en-en-us.pdf](#)

### Characteristic curve

[eaton-xeffect-faz-mcb-characteristic-curve.jpg](#)

[eaton-mcb-characteristic-xeffect-faz-t-characteristic-curve.eps](#)

### Declarations of conformity

[DA-DC-03\\_FAZT](#)

### Drawings

[eaton-xeffect-faz-mcb-dimensions-002.jpg](#)

[eaton-mcb-xeffect-faz-t-dimensions.eps](#)

[eaton-mcb-faz-xeffect-faz-3d-drawing-002.eps](#)

[eaton-xeffect-faz-t-mcb-3d-drawing.jpg](#)

[eaton-xeffect-faz-t-mcb-3d-drawing-007.jpg](#)

[eaton-xeffect-faz-t-mcb-3d-drawing-004.jpg](#)

### eCAD model

[DA-CE-ETN.FAZT-D10\\_2](#)

### Installation instructions

[IL019140ZU](#)

### mCAD model

[faz\\_1pn\\_2p.stp](#)

[faz\\_1pn\\_2p.dwg](#)

### PEP Eco-passport

[EATO-00047-V01.01-EN](#)

### Wiring diagrams

[eaton-mcb-xeffect-faz-wiring-diagram-002.eps](#)

[eaton-xpole-mmc4-6-m-mcb-wiring-diagram-003.jpg](#)

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Frame

45 mm

#### Frequency rating

50 Hz / 60 Hz

#### Pollution degree

2

#### Mounting Method

Quick attachment with 3 latch positions for top-hat rail IEC/EN

60715

#### Degree of protection

IP20

#### Equipment heat dissipation, current-dependent

3 W

#### Rated impulse withstand voltage (Uimp)

4 kV

#### Busbar material thickness

0.8 mm (except N 0.5 SU)

#### Terminal protection

Finger and hand touch safe, DGUV VS3, EN 50274

#### Terminals (top and bottom)

Twin-purpose terminals

#### Tripping characteristic

D

#### Ambient operating temperature - max

75 °C

#### Ambient operating temperature - min

-25 °C

#### Built-in depth

70.5 mm

#### Connectable conductor cross section (multi-wired) - max

25 mm<sup>2</sup>

#### Connectable conductor cross section (multi-wired) - min

1 mm<sup>2</sup>

#### Connectable conductor cross section (solid-core) - max

25 mm<sup>2</sup>

#### Connectable conductor cross section (solid-core) - min

1 mm<sup>2</sup>

#### Current limiting class

3

Enclosure width

80 mm

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Heat dissipation capacity

0 W

Heat dissipation per pole, current-dependent

0 W

Direction of incoming supply

As required

Voltage rating (IEC/EN 60898-1)

400 VAC

Width in number of modular spacings

2

Voltage rating (IEC/EN 60947-2)

240 V AC / 415 V AC

Voltage type

AC

Mounting position

As required

Lifespan, mechanical

10000 operations

Overvoltage category

III

Number of poles

Two-pole

Lifespan, electrical

4000 operations

Release characteristic

D

Mounting width

17.5 mm

Mounting width per pole

17.5 mm

Number of poles (protected)

2

Number of poles (total)

2

Operational voltage (IEC/EN 60947-2) - max

415 VAC

Operational voltage at DC (EC/EN 60947-2) - max

60 VDC

Rated insulation voltage (Ui)

440 V

Rated operational current for specified heat dissipation (In)

10 A

Rated operational voltage (Ue) - max

415 V

Rated short-circuit breaking capacity (EN 60898) at 230 V

15 kA

Rated short-circuit breaking capacity (EN 60898) at 400 V

15 kA

Rated short-circuit breaking capacity (IEC 60947-2) at 230 V

25 kA

Rated short-circuit breaking capacity (IEC 60947-2) at 400 V

25 kA

Rated switching capacity (IEC/EN 60947-2)

25 kA

Static heat dissipation, non-current-dependent

0 W

Terminal capacity

1 mm<sup>2</sup> - 25 mm<sup>2</sup>

Tightening torque

Max. 2.4 Nm

Power loss

3 W



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)