

DeWalt DCD706D2A-B1

12V XTREME™ Hammer Drill 2.0Ah x2

Introduction

The **DCD706D2A-B1 12V MAX* XR® Brushless Sub-Compact Hammer Drill/Driver Kit** is a lightweight, high-performance tool engineered for powerful drilling and fastening in ultra-tight spaces. Driven by an efficient brushless motor that delivers up to 57.5 Nm of torque, this compact hammer drill features a 2-speed transmission and a 15-position clutch to ensure optimal control across various applications. Designed with an integrated hammer function, a bright LED work light, and a 10mm ratcheting chuck, it effortlessly tackles masonry, wood, and metal. This versatile kit comes complete with two 2.0Ah batteries, a charger, a heavy-duty storage bag, and a premium 29-piece accessory set, making it the perfect all-in-one solution for trade professionals.

Key Features

- DEWALT built brushless motor for efficient performance and runtime
- 10mm ratcheting chuck for a wide variety of bits
- 2-Speed transmission and 15 clutch settings for a variety of applications

Specifications Table

Specification	Details
Voltage	10.8 / 12V
Battery	2 x 2.0 Ah
Charger	Yes
No load speed 1st gear	0 - 425 min-1
No load speed 2nd gear	0 - 1500 min-1
Beats per minute 1st gear	0 - 7225 min-1
Beats per minute 2nd gear	0 - 25500 min-1
Max. torque soft	23.5 Nm
Max. torque hard	57.5 Nm
Chuck capacity mm	10 mm
Maximum drilling capacity (Wood)	20 mm
Maximum drilling capacity (Metal)	10 mm
Maximum drilling capacity (Masonry)	10 mm
Weight (without battery pack)	0.96 kg