



## Main

Range	Odace
Product or component type	Connected socket-outlet
Concentrator compatibility	Wiser hub generation 2
Mobile App name	Wiser Home
Device presentation	Mechanism with fixing frame
Socket-outlet type	Single socket-outlet
Socket number	1
Outlet poles configuration	2P + E
Outlet standard	CEE 7/5
Main colour tint	Aluminium

## Complementary

Device mounting	Flush
Rated current	16 A
Load type	LED lamp 125 µF 100 W 230 V AC Incandescent lamp 2000 W 230 V AC Low voltage halogen lamp with ferromagnetic transformer 1500 VA Low voltage halogen lamp with electronic transformer 2000 VA Resistive 3680 W Capacitive 70 µF 6 AX Inductive 16 A cos phi = 0.6 Motor 1600 VA 7 A
Number of power socket outlets	1 x connected
[Ue] rated operational voltage	230 V AC 50 Hz
Standby consumption	Max. 0.4 W
Protection device type	Miniature circuit breaker (MCB) 16 A max
Protection type	Overheating protection Overload protection
Function available	Power monitoring
Measurement accuracy	+/- 1 % (at > 25 W load)
Communication network type	Wireless Zigbee (2405...2480 MHz), 10 mW at < 50 m
Colour tint	Aluminium
Surface finish	Matt
Surface treatment	Painted
IP degree of protection	IP20
Local signalling	LED (green/red/orange)
Signalling function	Status
Control type	By mobile application
Connections - terminals	Screwless terminals
Clamping connection capacity	2 x 2.5 mm <sup>2</sup>
Material	Thermoplastic
Fixing mode	By screws
Type of installation	Indoor
Embedding depth	31.55 mm
Depth	43.35 mm
Width	72.7 mm

Height	72.7 mm
Projecting depth	11.8 mm
Product certifications	Zigbee 3.0

## Environment

Ambient air temperature for operation	5...40 °C
IK degree of protection	IK02

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Halogen content performance	Halogen free plastic parts product