

PRODUCT DATASHEET

PL COMP 1200 V 26W 840 U19

PANEL COMPACT 1200 | Rectangular recessed panel luminaires, 1200 x 300 mm



Areas of application

- Suitable for recessed ceiling systems with grid size of 1200 x 300 mm
- Direct replacement for recessed luminaires with fluorescent lamps
- Offices, conference rooms
- Reception areas, foyers, corridors, elevators

Product benefits

- Energy savings thanks to system efficacy of up to 140lm/W
- High color consistency with SDCM 3
- Through-wiring possible
- Decentral emergency lighting possible with separately available LEDVANCE Emergency Conversion Box
- Versions with reduced glare (U19) for office applications available

Product features

- Extruded aluminum frame, metal housing
- Polystyrene diffuser
- Lifetime (L80/B10): up to 75,000 h (at 25 °C)
- 3-pole terminal block, cable cross section up to 3 x 1.5 mm²
- Type of protection: IP50 (panel luminaire), IP20 (driver)




TECHNICAL DATA

Electrical data


Nominal wattage	26.00 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz
Nominal current	120.000 mA
Inrush current	28 A
Inrush current time T_{h50}	95 μ s
Max. number of luminaires per miniature circuit breaker B16	25
Max. number of luminaires per miniature circuit breaker C10	21
Max. number of luminaires per miniature circuit breaker C16	34
Power factor λ	0.90
Protection class	II
Surge capability (L-N)	1000 V
Operating mode	External LED driver

Photometrical data

Luminous flux	3640 lm
Luminous efficacy	140 lm/W
Color temperature	4000 K
Light color (designation)	Cool White
Color rendering index Ra	> 80
Standard deviation of color matching	< 3 sdc _m
Low flicker	Yes
Flickering metric (Pst LM)	<1
Stroboscope effect metric (SVM)	< 0.4
Photobiological safety group acc. to EN62778	RG0
Photobiological safety group acc. to EN62471	RG0
Beam angle	90 °
UGR	< 19




PL COMP 1200 V 26W 840 U19 3640lm



PL COMP 1200 V 26W 840 U19 3640lm

Dimensions & Weight

Length	1195.00 mm
Width	295.00 mm
Height	34.00 mm
Product weight	1650.00 g



PL COMP1200 V

Materials & Colors

Product color	White
Housing color	White
RAL Color (most similar)	RAL 9003
Body material	Aluminum
Cover material	Polystyrene (PS)
Light emitting surface material	Polystyrene
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-10...+45 °C
Temperature range at storage	-20...+70 °C
Type of connection	Screwless terminal
Type of protection	IP50/IP20
Protection class IK (shock resistance)	IK02
Dimmable	No
Mounting type	Recessed/Suspended/Surface
Mounting location	Ceiling
Application environment	Indoor
Mounting length	1175 mm
Mounting width	575 mm
Mounting depth	50 mm
Mechanically adjustable	No
With light source	Yes
Replaceable light source	No

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	75000 h ¹⁾
Lifespan L80/B50 at 25 °C	75000 h
Lifespan L90/B10 at 25 °C	35000 h
Number of switching cycles	100000

¹⁾ t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	700 mA
----------------	--------

ECG - Output ripple current	0.05 %
ECG - Length	175.00 mm
ECG - Width	55,0 mm
ECG - Height	30,0 mm
Recommended control gear	DR DS-V-26/220-240/700 PL COMP

Emergency lighting

Type of Emergency Lighting (EL)	Optional EL unit (battery and controller) for decentral operation available separately
Wattage in emergency operation mode	4 W
Luminous flux in emergency operation mode	500

Certificates & Standards

Standards	CE / CB / ENEC / UKCA / EAC / EPD
Luminaire with limited surface temperature, "D sign"	No
Ball shot safe	No
EPD	LEDV-00075-V01.01-EN
Replaceable light source (EPREL)	Not replaceable

Accessories Optional

Product image	Product name	EAN
	PANEL 1200 X 300 SF MOUNT KIT H70 VAL	4099854018497
	PANEL 1200x300 RECESSED MOUNT FRAME	4058075472976
	PANEL RECESSED MOUNT CLIPS VAL 4x	4058075409859
	PANEL Suspension Kit	4058075402928

EQUIPMENT / ACCESSORIES

- Accessories for several mounting options available
- Security rope for luminaire included
- Security brackets preinstalled
- External control gear included
- Suitable for use with separate Emergency Conversion Box
- Replacement driver separately available

Upgrade and replacement components

Components EL Battery		
-----------------------	--	--

Product image	Product name	EAN
	EL KIT COMP 55V 4W LI MT AT 3H WT	4058075860711

Components Driver		
-------------------	--	--

Product image	Product name	EAN
	DR DS-V 26/220-240/700 PL COMP	4099854748813

Safety advice

- All electrical connections must be made by a qualified person.
- The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire must be disposed of.
- Caution, risk of electric shock.
- The luminaires are not suitable for covering with thermally insulated material.

DOWNLOAD DATA

Documents and certificates		Document name
	User instruction / safety instructions	G11256087 PL COMP
	Legal information	Safety Insert G11207793
	Legal information	Legal Insert G11146927


Documents and certificates		Document name
	Legal information	Informationstext 18 Abs 4 ElektroG
	Legal information	LSI PANEL COMPACT GEN2 1200
	Legal information	PL COMP
	Declarations of conformity	PANEL COMPACT
	Declarations of conformity UKCA	PANEL COMPACT
	EPD	EPD_EN_PANEL COMPACT GEN 2
	EPD	EPD_FR_PANEL COMPACT GEN 2
Photometric and lighting design files		Document name
	IES file (IES)	PL COMP 1200 V 26W 840 U19 3640lm
	LDT file (Eulumdat)	PL COMP 1200 V 26W 840 U19 3640lm
	ULD file (DIALux)	PL COMP 1200 V 26W 840 U19
	ROLF file (RELUX)	PL COMP 1200 V 26W 840 U19
	UGR file (UGR table)	PL COMP 1200 V 26W 840 U19 3640lm
	Light distribution curve type cone	PL COMP 1200 V 26W 840 U19 3640lm
	Light distribution curve type polar	PL COMP 1200 V 26W 840 U19 3640lm
CAD/BIM files		Document name
	BIM Revit 3D	Panel Compact G2
	CAD STEP 3D	PL COMP G2 1200
Tender texts		Document name
	Tender documents	PANEL COMPACT 1200 26W 840 U19-en

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854735684	Folding box 1	40 mm x 302 mm x 1,314 mm	2030.00 g	15.87 dm³
4099854735691	Shipping box 4	1,330 mm x 180 mm x 330 mm	9280.00 g	79.00 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION



References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.