



## COBA-Switch

### Purpose-designed switchboard matting

- Provides safety for operatives against electrical shocks.
- For use in front of switchboards and high voltage equipment.
- Slip-resistant fine fluted surface.
- 6mm tested to 11,000 volts for 450 volt rated working.
- 9.5mm tested to 15,000 volts for 650 volt rated working.
- 9.5mm conforms to BS921/1976.

Product height: 6mm or 9.5mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 10 (6mm)	87	29 x 29 x 90	Roll	1	6	Black	SM010010
0.9 x per linear metre (6mm)	9	10 x 10 x 90	Roll	1	N/A	Black	SM010010C
1.2 x 10 (6mm)	116	35 x 35 x 90	Roll	1	6	Black	SM010020
1.2 x per linear metre (6mm)	12	12 x 12 x 120	Roll	1	N/A	Black	SM010020C
0.9 x 10 (9.5mm)	137	37 x 37 x 90	Roll	1	6	Black	SM010030
0.9 x per linear metre (9.5mm)	14	14 x 14 x 90	Roll	1	N/A	Black	SM010030C
1.2 x 10 (9.5mm)	183	37 x 37 x 120	Roll	1	6	Black	SM010040
1.2 x per linear metre (9.5mm)	18	16 x 16 x 120	Roll	1	N/A	Black	SM010040C

Material:	Natural rubber base Polymer
Hardness:	650 C +/-50 Shore A
Specific Gravity:	1.56 g/cm <sup>3</sup>
Surface Finish:	2mm high ribbed pattern providing safe working with standard 3 phase 450 volt working.
Product Height:	6 mm nominal
Tensile Strength:	5 MPA
Elongation:	250%
Compression Set (22h@700 C):	-28°C
Heat ageing 160 hours @ 700 C:	
Change in Hardness	+2 IRHD
Change in Tensile	-8%
Change in Elongation	-12%
Dialectric Strength	5KV/mm
Electrical Breakdown Strength	11KV minimum
Leakage Current	160mA/m <sup>2</sup> max
Weight	10kg/m <sup>2</sup> approx.

Continued on next page

#### United Kingdom

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

+44 (0)116 240 1088  
sales@cobaeurope.com  
www.cobaeurope.com

#### Germany

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

+49 (2161) 2945-0  
verkauf@cobaeurope.de  
www.cobaeurope.de

#### Slovakia

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

+421 41 507 11 12  
sales@cobaeurope.sk  
www.cobaeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

Environmental Resistance:

Use in dry areas.

UV Resistance:

Yes

Typical Applications:

Suitable for use in high voltage areas. Specifically designed for use in front of open switchboards or high voltage equipment. Product ensures safety for operators against electrical shocks.

Installation Method:

Loose lay

Cleaning method:

Hose down or pressure wash using a mild detergent.


Product Performance:

Fatigue:

Slip Resistance:

Wear:

Low ≠ High



Flame Retardancy:

N/A

Country of Origin:

China

## Chemical Data

6mm

Major components: Natural Rubber (NR), Styrene-Butadiene Rubber (SBR), White Carbon black  
Minor components: Zinc Oxide, Sulfur, Accelerators / Activators (< 1%), Antioxidant / Stabilizers (< 1%)

9.5mm

Major components: Natural Rubber (NR), Styrene-Butadiene Rubber (SBR), White Carbon black  
Minor components: Zinc Oxide, Sulfur, Accelerators / Activators (< 1%), Antioxidant / Stabilizers (< 1%)

End of document

### United Kingdom

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

+44 (0)116 240 1088  
sales@cobaeeurope.com  
www.cobaeeurope.com

### Germany

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

+49 (2161) 2945-0  
verkauf@cobaeeurope.de  
www.cobaeeurope.de

### Slovakia

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

+421 41 507 11 12  
sales@cobaeeurope.sk  
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.