



Part Number : [988231010](#)
Product Description : NSCC Male Housing, Terminal
Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits,
White
Series Number : 98823
Status : Not Recommended For New Design
Product Category : Connector Housings
Engineering Number : 08119EV10F9



Documents & Resources

Drawings

- [988231010 sd.pdf](#)
- [PK-31301-635-001.pdf](#)
- [PK-31301-635-001.pdf](#)

Specifications

- [AS-98816-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	98823
Description	NSCC Male Housing, Terminal Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits, White
Application	Power, Wire-to-Wire
Comments	Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
Product Name	NSCC
UPC	822348817177

Physical

Circuits Detail	10x1.5mm pins
Circuits (maximum)	10
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	8.000/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	3.33mm, 6.00mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +100°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC Unsealed Female Housing, 10 Circuits, Dual Row, White, Version 2 with Ear	<u>988161010</u>
NSCC Unsealed Female Housing, 10 Circuits, Dual Row, White, Version 1 without Ear	<u>988161110</u>

Use with Part(s)

Description	Part Number
Use With	Use with FCI Male Terminals